

[See all 35 Products in Family](#)

**TECHSPEC® 355nm, 50mm Diameter, OD 4.0 Notch Filter**



TECHSPEC OD 4.0 Notch Filters

Stock **#67-124** **1 In Stock**

[Additional Bandwidths](#)

⊖ 1 ⊕ €1.010<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €1.010,00 each                |
| Qty 6-25       | €859,00 each                  |
| Qty 26-49      | €799,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

**!** Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Notch Filter **Type:**

**Physical & Mechanical Properties**

50.00 +0.00/-0.10 **Diameter (mm):**

|  |                                  |
|--|----------------------------------|
| 42.5   | <b>Clear Aperture CA (mm):</b>   |
| 5.00 ±0.1  | <b>Thickness (mm):</b>           |
| Mounted in Black Anodized Ring   | <b>Construction:</b>             |
| <b>Physical Durability:</b><br>Adhesion per ML-PRF-13830B, Section C.4.5.12<br>Moderate abrasion per ML-PRF-13830B, Section C.4.5.11<br>Cleaning per ML-C-48497A Section 4.5.4.2 |                                  |
| 3.5 ±0.5   | <b>Substrate Thickness (mm):</b> |

## Optical Properties

|             |                                       |
|-------------|---------------------------------------|
| ≥4.0        | <b>Optical Density OD (Average):</b>  |
| 355.00      | <b>Center Wavelength CWL (nm):</b>    |
| 355         | <b>Design Wavelength DWL (nm):</b>    |
| 17.80       | <b>Full Width-Half Max FWHM (nm):</b> |
| Hard Coated | <b>Coating:</b>                       |
| 60-40       | <b>Surface Quality:</b>               |
| 90          | <b>Transmission (%):</b>              |
| 325 - 475   | <b>Transmission Wavelength (nm):</b>  |
| 99          | <b>Reflection at CWL (%):</b>         |
| <1λ         | <b>Transmitted Wavefront, RMS:</b>    |

## Threading & Mounting

|     |                              |
|-----|------------------------------|
| 5.0 | <b>Mount Thickness (mm):</b> |
|-----|------------------------------|

## Environmental & Durability Factors

|   |  |
|---|--|
| <b>Environmental Durability:</b><br>Humidity per ML-STD-810H, Section 507.6<br>Temperature per ML-STD-810H, Section 501.7 and 502.7 |  |
|---|--|

## Regulatory Compliance

|                  |                                    |
|------------------|------------------------------------|
| <b>Compliant</b> | <b>RoHS 2015:</b>                  |
| <b>View</b>      | <b>Certificate of Conformance:</b> |
| <b>Compliant</b> | <b>Reach 247:</b>                  |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- >OD 4.0 Rejection of Laser Wavelength from 355nm to 1064nm
- Broad Transmission Range
- [OD 6.0 Notch Filters Also Available](#)
- Low Cost Alternative to Rugate Notch Filters

TECHSPEC® OD 4.0 Notch Filters are low-cost alternatives to Rugate Notch Filters. The filters feature narrow rejection bands of just ±2.5% of the center wavelength while offering greater than 99% reflection of the laser wavelength. These optical filters have a broad transmission range and are hard coated to guarantee performance that will not degrade with time, temperature, or humidity. TECHSPEC® OD 4.0 Notch Filters are mounted in a black anodized ring engraved to ease filter handling, identification, and orientation. [OD 6.0 Notch Filters](#) are also available for purchase.

**Note:** These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). Atypical LIDT for these filters is 1 J/cm<sup>2</sup> @ 532nm, 10ns. Please [contact us](#) if you require a filter with a higher LIDT value.

## Technical Information



*This graph is an example of a standard notch filter transmission curve. For specific wavelength data, please refer to the curve PDF attached to each respective part.*



*All mounted TECHSPEC® Optical Filters have an arrow on the side of the mount that points to the filter-coated surface for quick reference. Filter oriented such that arrow points to filter coated surface S1. Anti-reflective (AR) coating is applied to S2.*

## Compatible Mounts