

38.1mm Dia., 5mm Thick, Uncoated, ISP Optics Barium Fluoride (BaF₂) Window | BF-W-38-5

See More by [ISP Optics](#)



Stock **#24-501** CLEARANCE CONTACT US

-

1

+

€102^{.98} ~~€205,95~~

ADD TO CART

Volume Pricing	
Qty 1+	€205,95 €102,98 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Protective Window

Type:

BF-W-38-5	Model Number:
Physical & Mechanical Properties	
Protective as needed	Bevel:
85	Clear Aperture (%):
32.38	Clear Aperture CA (mm):
38.10 +0.00/-0.13	Diameter (mm):
5.00 ±0.13	Thickness (mm):
Fine Ground	Edges:
82.00	Knoop Hardness (kg/mm²):
<3	Parallelism (arcmin):
0.34	Poisson's Ratio:
53	Young's Modulus (GPa):
Optical Properties	
81.78	Abbe Number (v _d):
Random	Axis Orientation:
Uncoated	Coating:
1.48	Index of Refraction (n _d):
Barium Fluoride (BaF ₂)	Substrate:
2λ	Surface Flatness (P-V):
40-20	Surface Quality:
200 - 12000	Wavelength Range (nm):
Material Properties	
18.1	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
4.89	Density (g/cm³):
Environmental & Durability Factors	
Maximum: 800	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

PRODUCT DETAILS

- Excellent Transmission from 0.2 - 12μm
 - Resistant to High-Energy Radiation
 - High Transmission without AR Coatings
- ISP Optics Barium Fluoride (BaF₂) Windows provide excellent transmission from 0.2- 12μm without the need for an Anti-Reflection (AR) coating due to its low index of refraction. Barium Fluoride has similar physical properties to Calcium Fluoride, but features higher resistance to high-energy radiation. This makes Barium Fluoride ideal for vacuum UV (VUV) applications such as thermography or laser spectroscopy where high radiation resistance is required. ISP Optics Barium Fluoride (BaF₂) Windows can be used up to 800°C in a dry environment, but prolonged exposure to moisture can degrade transmission in the ultraviolet range.
- Note:** These optical windows are very sensitive to thermal shock.

SPECIAL HANDLING

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

