

38.1mm Dia. x 38.1mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF₂) DCX Lens | CF-BX-38-38

See More by [ISP Optics](#)



Calcium Fluoride Double-Convex (DCX) Lenses

Stock **#24-766** CLEARANCE CONTACT US

-

1

+

€211ST €423,33

ADD TO CART

Volume Pricing	
Qty 1-9	€423,33 €211,67 each
Qty 10+	€381,10 €190,55 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:


Double-Convex Lens	
CF-BX-38-38	Model Number:
Physical & Mechanical Properties	
38.10 +0.00/-0.13	Diameter (mm):
<3	Centering (arcmin):
Protective as needed	Bevel:
17.70 ±0.20	Center Thickness CT (mm):
2.50	Edge Thickness ET (mm):
34.29	Clear Aperture CA (mm):
Optical Properties	
38.10 @ 5µm	Effective Focal Length EFL (mm):
Uncoated	Coating:
Calcium Fluoride (CaF ₂)	Substrate:
60-40	Surface Quality:
λ	Irregularity (P-V) @ 632.8nm:
27.61	Radius R ₁ (mm):
27.61	Radius R ₂ (mm):
1.00	f/#:
±2	Focal Length Tolerance (%):
0.5	Numerical Aperture NA:
300 - 8000	Wavelength Range (nm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

PRODUCT DETAILS


- Greater than 90% Transmission from 350nm-7µm
- Low Index of Refraction
- High Laser Damage Threshold

ISP Optics Calcium Fluoride Double-Convex (DCX) Lenses are ideal for finite imaging applications requiring high transmission in the infrared wavelength spectrum. Calcium Fluoride features greater than 90% transmission from 350nm to 7µm and a low refractive index, allowing it to be used without an antireflective coating. In addition, its low absorption and high damage threshold makes it a popular choice for use with excimer lasers. ISP Optics Calcium Fluoride Double-Convex (DCX) Lenses offer low solubility and superior hardness compared to other fluoride-based substrates, allowing for use in harsh environments.


TECHNICAL INFORMATION



Calcium Fluoride



Uncoated



SPECIAL HANDLING

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools