

[See all 71 Products in Family](#)

**TECHSPEC® 400 - 750nm, 25mm Dia., Dichroic Shortpass Filter Kit (8 Filters)**



Stock #15-106 [CONTACT US](#)

⊖ 1 ⊕ €1.387<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€1.387,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

**Filters Included :**  
Cut-off Wavelengths: [400nm](#), [450nm](#), [500nm](#),  
[550nm](#), [600nm](#), [650nm](#), [700nm](#), [750nm](#)

**Type:**  
Shortpass Filter

**Number of Filters:**  
8

**Physical & Mechanical Properties**

**Diameter (mm):**

**Physical Durability:**

Adhesion per ML-PRF-13830B, Section C.4.5.12  
Moderate abrasion per ML-PRF-13830B, Section C.4.5.11  
Cleaning per ML-C-48497A Section 4.5.4.2

**Environmental & Durability Factors**

**Environmental Durability:**

Humidity per ML-STD-810H, Section 507.6  
Temperature per ML-STD-810H, Section 501.7 and 502.7

**Regulatory Compliance**

**Certificate of Conformance:**

[View](#)

**Product Details**

- Sharp Cut-Off Wavelength
- Broad Transmission and Reflection Ranges
- Available in a Range of Common Sizes

Our TECHSPEC® Dichroic Shortpass Filters are designed for a 45° angle of incidence. The rejected light is reflected at 90°, making these filters ideal for use in fluorescence applications or as spectral beamsplitters. The filters feature low polarization dependence, broad spectral ranges, and a precision fused silica substrate. TECHSPEC® Dichroic Shortpass Filters have a sharp cut-off wavelength and are available in a wide range of sizes for ease of system integration. These filters can be combined with TECHSPEC® Dichroic Longpass Filters to create custom bandpass filters.

**Note:** The chevron on the edge of the filter points towards surface S1 with the primary filter coating on which the light should be incident.

**Technical Information**

