

[See all 2 Products in Family](#)

**TECHSPEC® 4.0mm Diameter, S-LAH79 Half-Ball Lens**



Stock #90-859 **20+ In Stock**

⊖ 1 ⊕ €122.<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | €122,00 each                  |
| Qty 11-49      | €110,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Half-Ball Lens **Type:**

**Physical & Mechanical Properties**

4.00 **Diameter (mm):**

2.00 **Radius R (mm):**

+0/-1.5      Radius Tolerance ( $\mu\text{m}$ ):

2.00  $\pm$ 0.05      Thickness (mm):

## Optical Properties

S-LAH79      Substrate:

Uncoated      Coating:

400 - 2400      Wavelength Range (nm):

## Regulatory Compliance

Compliant      RoHS 2015:

View      Certificate of Conformance:

Compliant      Reach 247:

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- 2.0 Index of Refraction
- Simplifies System Integration
- [High Index Ball Lenses](#) Also Available

TECHSPEC® High Index Half-Ball Lenses feature a higher index of refraction compared to our LaSFN9 ball lenses and provides a shorter back focal length, simplifying fiber coupling. These lenses are available in various diameter options, all with S-LAH79 (Ohara) substrate. TECHSPEC® High Index Half-Ball Lenses simplify system integration and are used in various applications such as endoscopy and bar code scanning. [Contact us](#) today to discuss custom options.

## Technical Information

