

[See all 57 Products in Family](#)

**TECHSPEC® 40mm Diameter, T-Mount Thick Optic Mount**



Stock #57-978 **3 In Stock**

- 1 + €72.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	€72,00 each
Qty 5-9	€64,10 each
Qty 10-25	€59,30 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Fixed **Type:**

Circular **Type of Optics:**

**Function:**

## Physical & Mechanical Properties

25.0 **Extension Length (mm):**

**Construction:**  
Black Anodized Aluminum (6061 T6)

28.45 **Total Length (mm):**

48.0 **Outer Diameter (mm):**

38.0 **Clear Aperture CA (mm):**

20.95 **Max. Thickness of Compatible Optics (mm):**

5.0 **Min. Thickness of Compatible Optics (mm):**

## Threading & Mounting

40.0 **Diameter of Compatible Optics (mm):**

T-Mount **Thread Type:**

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**REACH 241:**  
[Compliant](#)

## Product Details

- Mounts for Simple Lenses, Achromats, Filters, or Reticles
- Designed to Integrate with Any C, S, or T-Mount Components
- Optic is Held in Place with Included Retaining Ring

TECHSPEC® C, S, and T-Mount Circular Optic Mounts are designed to mount a variety of circular optical components into C, S, or T-Mount compatible systems. An included threaded retainer ring, designed to accept a standard spanner wrench, securely holds the optical component. These circular optic mounts are compatible with a wide variety of Edmund Optics optomechanical components utilizing C, S, or T-Mount threads, such as [extension tubes](#) and [kinematic mounts](#). TECHSPEC® C, S, and T-Mount Circular Optic Mounts are threaded for 1" x 32TPI, M12 x 0.5, or M42 x 0.75 mounting, with 30mm, 16mm, and 48mm outer diameters, respectively. These mounts are ideal for creating and personalization of a diverse range of optical systems.

**Note:** [#56-353](#), [#56-354](#), [#52-933](#), and [#52-292](#) are all 3-part assemblies

## Technical Information

