

[See all 5 Products in Family](#)

40X Objective, S Plan Fluor ELWD

See More by [Nikon](#)



Stock #75-372 NEW **1 In Stock**

⊖ 1 ⊕ €3.045⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€3.045,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

MRH08430 **Model Number:**

Compatible Tube Lens Focal Length (mm):
Focal Length: 200mm

Microscope Objective **Type:**

Infinity Corrected **Style:**

Nikon

Manufacturer:

Physical & Mechanical Properties

0.55 Field of View (mm):

56.11 Length excluding Threads (mm):

34 Maximum Diameter (mm):

200 Weight (g):

Optical Properties

0-2 Compatible Cover Glass Thickness (mm):

0.025 Horizontal Field of View, 1/2" Sensor:

0.22 Horizontal Field of View, 2/3" Sensor:

40X Magnification:

0.60 Numerical Aperture NA:

2.8-3.6 Working Distance (mm):

22 Field Number (mm):

60.41 Parfocal Length (mm):

N/A Immersion Liquid:

Sensor

2/3" Maximum Sensor Format:

Threading & Mounting

M25 x 0.75 Mounting Threads:

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Extra-Long Working Distance (ELWD)
- Broad Spectral Transmittance
- Versatility in Observation Modes

Nikon CFI S Plan Fluor ELWD Objectives are designed with an extra-long working distance to allow for high-resolution imaging of large samples and culture vessels of varying thicknesses. With broad spectral transmittance, from near-ultraviolet to near-infrared wavelengths, these objectives enable versatile imaging across multiple advanced microscopy techniques. These objectives allow for greater flexibility and protect delicate specimens during observations by not requiring immersion media. Nikon CFI S Plan Fluor ELWD Objectives are available in a variety of magnifications and support common observation modes, including brightfield, darkfield, DIC, phase contrast, and polarizing microscopy. These objectives are ideal for general fluorescence, brightfield, calcium imaging, and DIC applications.

Technical Information

