

[See all 4 Products in Family](#)

## 457nm 25.4mm META® holoOPTIX® STRATA Notch Filter



25.4mm META® holoOPTIX® STRATA Notch Filter

Stock #23-024 CLEARANCE **3 In Stock**

€364<sup>MS</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€364,95 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Notch Filter **Type:**

#### Physical & Mechanical Properties

25.40 ±0.2 **Diameter (mm):**

20 **Clear Aperture CA (mm):**

**Thickness (mm):**

4.50 ±0.1

**Construction:**

Mounted in Black Anodized Ring

**Clear Aperture (%):**

80

**Optical Properties**

**Optical Density OD (Average):**

>4.0

**Center Wavelength CWL (nm):**

457.00

**Surface Quality:**

60-40

**Transmission (%):**

84% (400-435nm)  
96% (500-750nm)

**Transmitted Wavefront, RMS:**

<1λ

**Spectral Bandwidth @ OD1:**

8 (Typical)

**Threading & Mounting**

**Mount Thickness (mm):**

4.5

**Regulatory Compliance**

**Certificate of Conformance:**


[View](#)

**Product Details**

- >OD 4.0 (Typical)
- Broad Transmission Range
- Unique Large Flexible Design
- META® refers to the registered trademark of Meta Materials Inc.

META® holoOPTIX® Notch Filters are ideal for laser analysis applications requiring specific wavelength rejection and high transmission of all other wavelengths. Available in either a standard 25.4mm rigid mounted configuration (STRATA) or in a unique 375mm x 70mm flexible configuration (FLEX), these filters can be used in fluorescence or Raman spectrometers to eliminate unwanted noise from the pump laser source to obtain the optimum signal-to-noise ratio. The flexible design can be easily be cut for system prototyping and integration. META® holoOPTIX® Notch Filters center wavelengths can be tuned by adjusting the angle of incidence while maintaining consistent notch center wavelengths for both p- and s- polarizations, even at high angles of incidence.

**Technical Information**



**Compatible Mounts**