

TECHSPEC® 460nm CWL, 25mm Dia., Hard Coated OD 4.0 10nm Bandpass Filter



TECHSPEC Hard Coated OD 4.0 10nm Bandpass Filters

Stock #88-010 3-4 DAYS

⊖ 1 ⊕ **€247,00**

ADD TO CART

Qty 1-5

€247,00

Qty 6+

€194,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Angle of Incidence (°):
0

Optical Density OD (Average):

≥4.0

Clear Aperture CA (mm):
21.0

Center Wavelength CWL (nm):
460.00 ±2.0

Full Width-Half Max FWHM (nm):
10.00 ±2.0

Full Width-Half Max FWHM Tolerance (nm):
±2.0

Substrate:
Optical Glass

Minimum Transmission (%):
>85

Coating:
Hard Coated

Surface Quality:
80-50

Thickness Tolerance (mm):
±0.1

Type:
Bandpass Filter

Typical Applications:
Styryl Absorption, Heterocycle/Benzimidazole
Emission

Blocking Wavelength Range (nm):
200 - 1200

Construction:
Mounted in Black Anodized Ring

Environmental Durability:
Humidity per ML-STD-810H, Section 507.6
Temperature per ML-STD-810H, Section 501.7 and
502.7

Physical Durability:
Adhesion per ML-PRF-13830B, Section C.4.5.12
Moderate abrasion per ML-PRF-13830B, Section
C.4.5.11
Cleaning per ML-C-48497A Section 4.5.4.2

Mount Thickness (mm):
5.0 ±0.1

Substrate Thickness (mm):
3.5 ±0.5 typical

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 223:
[Compliant](#)

Certificate of Conformance:
[View](#)