

TECHSPEC®

50mm, f/2.0 Sealed Cw Series Fixed Focal Length Lens



50mm Focal Length



Stock **#15-662** **9 In Stock**

-

1

+

€418^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€418,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Cw Series

Series:

C-Mbunt compatible with O-ring 25mm ID x2mm		Note:
Fixed Focal Length Lens		Type:
Physical & Mechanical Properties		
Fixed		Iris Option:
51.80		Length (mm):
41.00		Maximum Diameter (mm):
41		Outer Diameter (mm):
2.1		Maximum Rear Protrusion (mm):
Optical Properties		
Horizontal: 10.0° Vertical: 7.54° Diagonal: 12.5°		Field of View at Max Sensor Format:
10.0°		Horizontal Field of View, 2/3" Sensor:
8.22°		Horizontal Field of View, 1/1.8" Sensor:
7.31°		Horizontal Field of View, 1/2" Sensor:
6.58°		Horizontal Field of View, 1/2.5" Sensor:
5.49°		Horizontal Field of View, 1/3" Sensor:
11.00		Maximum Image Circle (mm):
0.043		Numerical Aperture NA, Object Side:
6 (5)		Number of Elements (Groups):
50.00		Focal Length FL (mm):
100 - ∞		Working Distance (mm):
f/2.0		Aperture (f/#):
425 - 675nm BBAR		Coating Specification:
41.82		Entrance Pupil Position (mm):
-11.85		Object Space Principal Plane (mm):
-38.15		Image Space Principal Plane (mm):
0.257		Maximum Distortion (%):
-40.88		Exit Pupil Position (mm):
VIS		Lens Wavelength Range:
Sensor		
2/3"		Maximum Sensor Format:
2.74		Pixel Size (μm):
Threading & Mounting		
M36 x0.50 (Female)		Filter Thread:
C-Mbunt		Mount:
Environmental & Durability Factors		
IPX7 and IPX9K		Environmental Rating:
		Storage Temperature (°C):

Type of Ruggedization:
Waterproof (IPX7 and IPX9K)

Regulatory Compliance

Certificate of Conformance:
[View](#)

PRODUCT DETAILS


- Up to 2/3", C-Mount Lens
- Waterproof (Cw) Versions of C Series Fixed Focal Length Lenses
- Meets IEC Ingress Protection Ratings of IPX7 and IPX9K
- Designed to Eliminate the Need for a Protective Lens Cover

TECHSPEC® Cw Series Fixed Focal Length Lenses are waterproof versions of our [TECHSPEC® C Series Fixed Focal Length Lenses](#). Designed to meet IEC Ingress Protection Codes IPX7 and IPX9K, these lenses withstand exposure to water up to 1 meter depth for 30 minutes and operate in close-range high pressure, high temperature water spray downs with the exception of all 3.5 and 4.5mm options which are IPX7. These lenses include a hydrophobic coated window to prevent water droplets from settling on the lens' surface. To prevent moisture from entering the housing, the lenses are sealed with multiple O-rings. TECHSPEC® Cw Series Fixed Focal Length Lenses are designed for up to 7.5 MegaPixel, 2/3" sensors and are ideal for applications including food, pharma, automotive, and security. These lenses won the Bronze-Level 2021 Vision Systems Design Innovators Award.


Edmund Optics has created a family of high performance optical designs (the C Series family) and developed 6 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the C Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- C Series:** Features locking cam focus and iris adjustment and is the most adjustable version of these optical designs; they are the typical high quality machine vision lenses. Also available with a [VIS-NIR Broadband Anti-Reflection \(BBAR\) Coating](#).
- CI Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.
- Cr Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.
- Cx Series:** Modular, flexible mechanics allows lenses to be taken apart for easy integration of accessories such as liquid lenses, apertures, and more.
- Liquid Lens Cx Series:** Designed with an integrated liquid lens for quick autofocus.
- Cw Series: Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 and IPX9K.


TECHNICAL INFORMATION




#15-662, 50mm, f/2.0 Sealed Cw Series Fixed Focal Length Lens, Distortion Plot




#15-662, 50mm, f/2.0 Sealed Cw Series Fixed Focal Length Lens, Relative Illumination Plot




#15-662, 50mm, f/2.0 Sealed Cw Series Fixed Focal Length Lens, Working Distance versus Field of View Plot



#15-662, 50mm, f/2.0 Sealed Cw Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f2



#15-662, 50mm, f/2.0 Sealed Cw Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f2



#15-662, 50mm, f/2.0 Sealed Cw Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 1000mm Working Distance, f2



#15-662, 50mm, f/2.0 Sealed Cw Series Fixed Focal Length Lens, Depth of Field Plot, 1000mm Working Distance, f2