

[See all 20 Products in Family](#)

## 600 Grooves, 12.7mm Square, 1600nm NIR Ruled Grating



Stock #54-850 **7 In Stock**

€155.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	€155,00 each
Qty 10-24	€139,50 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Reflective Diffraction Grating **Type:**

### Physical & Mechanical Properties

12.7 x 12.7 ±0.5 **Dimensions (mm):**

90 **Clear Aperture (%):**

Ruled Grating **Construction:**

Parallel to Short Dimension **Direction of Grooves:**

12.70 **Length (mm):**

6.00 ±0.5 **Thickness (mm):**

12.70 **Width (mm):**

±0.5 **Alignment of Grooves to Edge (°):**

### Optical Properties

600 **Groove Density (grooves/mm):**

700 - 3000 **Wavelength Range (nm):**

1600 **Blaze Wavelength (nm):**

28.68 **Blaze Angle (°):**

Bare Gold **Coating:**

Float Glass **Substrate:**

### Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **Reach 247:**



## Product Details

- Increased Reflection from 700 - 1100nm

Near-IR (NIR) Reflective Gold Gratings are ruled gold-coated versions of our commercial gratings. These gratings provide increased reflection from 700 - 1100nm. This makes them an excellent choice for applications such as fiber optic pulse compression and spectroscopy setups using [silicon detectors](#). Near-IR (NIR) Reflective Gold Gratings feature a float glass substrate and a ruled grating construction. The gratings are available in three sizes, with varying groove densities and blaze wavelengths.

**Handling Gratings:** Gratings require special handling, making them prone to fingerprints and aerosols. Gratings should only be handled by the edges. Before attempting to clean a grating, please [contact us](#).

## Technical Information



## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

---

;