

TECHSPEC® 632.8nm CWL, 12.5mm Dia, 2.4nm Bandwidth, OD6 Laser Line Bandpass Filter



Stock **#68-943** **2 In Stock**

[Additional Bandwidths](#)

⊖ 1 ⊕ €365.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€365,00 each
Qty 6-25	€292,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Bandpass Filter **Type:**

Physical & Mechanical Properties

12.50 **Diameter (mm):**

8.5 **Clear Aperture CA (mm):**

Optical Properties

0 ±2 **Angle of Incidence (°):**

2.4 **Bandwidth (nm):**

OD 5 Blocking Wavelength Range (nm) :
515.4 - 626.5 & 639.1 - 884.7

OD 6 Blocking Wavelength Range (nm):
582.2 - 623.3 & 642.3 - 696.1

≥6.0 **Optical Density OD (Average):**

632.80 **Center Wavelength CWL (nm):**

632.8 **Design Wavelength DWL (nm):**

4.40 **Full Width-Half Max FWHM (nm):**

Substrate:
[Fused Silica](#) (Corning 7980)

Hard Coated **Coating:**

60-40 **Surface Quality:**

≥90 **Transmission (%):**

λ/4 @ 633nm **Transmitted Wavefront, RMS:**

Threading & Mounting

3.5 **Mount Thickness (mm):**

Environmental & Durability Factors

Durability:
Environmental: ML-STD-810F, sect. 507.4
Durability: ML-C-48497A, sect. 3.4.1

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details


- Over 90% Transmission at Design Wavelength
- Hard Coated Design
- Designed for Laser Applications

Available for use with common gas and solid state lasers, TECHSPEC OD 6 Laser Line Clean-Up Filters are designed to offer maximum transmission of stimulated emission, while eliminating noisy spontaneous emission. TECHSPEC OD 6 Laser Line Clean-Up Filters are ideal for laser-based fluorescence instrumentation, Raman spectroscopy, or for analytical or medical laser systems. Due to their steep edges, TECHSPEC Laser Line Clean-Up Filters are excellent complements to [TECHSPEC Notch Filters](#) or [TECHSPEC Raman Longpass Edge Filters](#).


LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)


532nm Laser Line Bandpass Filter



1064nm Laser Line Bandpass Filter



785nm Laser Line Bandpass Filter



Compatible Mounts