

[See all 17 Products in Family](#)

## 75° Fan Angle, 500 - 850nm AR Coated, High Precision Powell Lens



Stock #70-144 **3 In Stock**

- 1 + €325.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	€325,00 each
Qty 11-49	€292,00 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Beam Shaping Lens **Type:**

### Physical & Mechanical Properties

8.90 +0.00/-0.15 **Dimensions (mm):**

8.90 +0.00/-2.00 **Height (mm):**

1.3 Input Beam Diameter,  $1/e^2$  (mm):

## Optical Properties

**N-SF6** Substrate:   
BBAR (500-850nm) Coating:

500 - 850 Wavelength Range (nm):

Coating Specification:  
 $R_{\text{abs}} < 1.0\%$  @ 500 - 700nm  
 $R_{\text{abs}} < 1.5\%$  @ 700 - 850nm

1.458 Index of Refraction ( $n_d$ ):

75.00 Fan Angle (°):

## Regulatory Compliance

[View](#) Certificate of Conformance:

## Product Details

- Generate Uniform, Flat-Top Profile Over Entire Line
- Fan Angles from 1° to 75° Available
- AR Coated for 400 - 500nm or 500 - 850nm

Precision Powell Lenses, also known as aspheric line generators (ALGs), spread an input beam across a uniform line with a top-hat beam profile at a specified fan angle. These Powell lenses are produced through a precision manufacturing process to ensure high contained power, uniformity, and line straightness across the entire produced line, as well as superior part-to-part consistency. They are designed for a specific input beam diameter to provide best line uniformity; larger input beams will result in higher intensity at the ends of the generated line, while smaller will create a more Gaussian distribution. Precision Powell Lenses are ideal for use in machine vision and life science applications including 3D profile measurement, PCB inspection, line-scan SD-OCT, line-scan confocal microscopy, flow cytometry, and particle analysis.