

[See all 8 Products in Family](#)

75 x 75mm, Rhodium Coated First Surface Mirror



Rhodium Coated First Surface Mirrors

Stock **#15-494** **2 In Stock**

-

1

+

€122⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€122,00 each
Qty 6-49	€98,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Flat Mirror

Type:

Physical & Mechanical Properties

75.0 x 75.0

Dimensions (mm):

±0.25

Dimensional Tolerance (mm):

Protective as needed	Bevel:
Seamed	Edges:
3.00 ±0.20	Thickness (mm):
75.00	Length (mm):
75.00	Width (mm):
Optical Properties	
4 - 6λ	Surface Flatness (P-V):
Float Glass	Substrate: □
80-50	Surface Quality:
R _{avg} >70% @400 - 700nm R _{avg} >90% @ 2000 - 10,000nm	Coating Specification:
Rhodium (400-10000nm)	Coating:
Metal	Coating Type:
400 - 10000	Wavelength Range (nm):
Environmental & Durability Factors	
Severe, per MIL-C-675C Paragraph 3.8.4.1	Coating Abrasion:
MIL-PRF-13830B, App B Para. 4.4.6	Coating Adhesion:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Corrosion and Extreme Abrasion Resistant Rhodium Coating
 - High Reflectivity in the VS and IR
 - Ideal for Orthodontic Applications
- Rhodium Coated First Surface Mirrors provide high reflectivity and are ideal for orthodontic applications, especially in intra-oral photography. These mirrors feature a rhodium coating, which is an element notably resistant to corrosion and aggressive chemicals and passes severe abrasion tests as per MIL-C-675C. Rhodium Coated First Surface Mirrors utilize a float glass substrate which enables easy customization and provides excellent cost to performance ratio. They are available in standard metric sizes, with either circular or square geometries.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts