

[See all 69 Products in Family](#)

## TECHSPEC® 75mm Diameter x 3.3mm Thickness, Uncoated, BOROFLOAT® Window

See More by [SCHOTT Optical Components](#)



TECHSPEC BOROFLOAT Borosilicate Windows

Stock #29-394 **20+ In Stock**

⊖ 1 ⊕ €37<sup>50</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €37,50 each                   |
| Qty 6-25       | €30,00 each                   |
| Qty 26-99      | €28,00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Protective Window **Type:**

Glass **Type of Window:**

### Physical & Mechanical Properties

|                      |  |
|----------------------|--|
| 67.50                | <b>Clear Aperture CA (mm):</b>             |
| 75.00 ±0.50          | <b>Diameter (mm):</b>                      |
| 3.30 ±0.2            | <b>Thickness (mm):</b>                     |
| Protective as needed | <b>Bevel:</b>                              |
| ≥90                  | <b>Clear Aperture (%):</b>                 |
| Ground and Seamed    | <b>Edges:</b>                              |
| 0.20                 | <b>Poisson's Ratio:</b>                    |
| 64                   | <b>Young's Modulus (GPa):</b>              |
| 480.00               | <b>Knoop Hardness (kg/mm<sup>2</sup>):</b> |

## Optical Properties

|                            |   |
|----------------------------|---|
| Uncoated                   | <b>Coating:</b>                             |
| <a href="#">BOROFLOAT®</a> | <b>Substrate:</b> □                         |
| 1.472                      | <b>Index of Refraction (n<sub>d</sub>):</b> |
| 80-50                      | <b>Surface Quality:</b>                     |
| 90                         | <b>Transmission (%):</b>                    |
| 65.41                      | <b>Abbe Number (v<sub>d</sub>):</b>         |
| 350 - 2000                 | <b>Wavelength Range (nm):</b>               |
| 4 - 6λ                     | <b>Surface Flatness (P-V):</b>              |

## Material Properties

|                      |   |
|----------------------|---|
| 2.23                 | <b>Density (g/cm<sup>3</sup>):</b>                                |
| 525                  | <b>Transformation Temperature (°C):</b>                           |
| 3.25 (+20 to +300°C) | <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b> |

## Environmental & Durability Factors

|  |  |
|--|--|
| 1 hour @ 500; >100 hours @ 450                                   | <b>Operating Temperature (°C):</b>               |
| Short Term, 1 hr: 110K 1 - 100 hrs: 90K Long Term, >100 hrs: 80K | <b>Resistance to Temperature Difference (K):</b> |
| Up to 4mm Thick: 175K 4 - 6mm Thick: 160K 6 - 15mm Thick: 150K   | <b>Thermal Shock (K):</b>                        |

## Regulatory Compliance

|                           |                                    |
|---------------------------|------------------------------------|
| <a href="#">Compliant</a> | <b>RoHS 2015:</b>                  |
| <a href="#">View</a>      | <b>Certificate of Conformance:</b> |
| <a href="#">Compliant</a> | <b>Reach 247:</b>                  |


## Product Details

- Low Coefficient of Thermal Expansion
- Visible to Near Infrared Transmission
- High Resistance to Thermal Shock

TECHSPEC® BOROFLOAT® Borosilicate Windows are ideal for high temperature and harsh environment applications. The windows have a low coefficient of thermal expansion of 3.25 (+20 to +300°C). TECHSPEC® BOROFLOAT® Borosilicate Windows feature visible to near infrared transmission. Unlike common borosilicate that is drawn flat, BOROFLOAT® is produced by a float technique that yields superior surface flatness — typically 4 - 6λ per inch. BOROFLOAT® is about three times more resistant to thermal shock than standard soda lime glass.

Can't find what you need? Get a quick [custom quote](#).

## Technical Information



**Quote Your Size**

**Compatible Mounts**

---