


TECHSPEC<sup>®</sup> 800 - 1150nm, 12.7mm Dia. Ultrafast-Enhanced Silver, Silicon, Laser Mirror



Stock #90-194 NEW 4 In Stock

-

1

+

€88<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €88,00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:  
Flat Mirror

Physical & Mechanical Properties

Parallelism (arcmin):  
<3

Clear Aperture (%):  
90

Back Surface:  
Commercial Polish

|                                    |                 |
|------------------------------------|-----------------|
| 12.70 +0.00/-0.10                  | Diameter (mm):  |
| 3.18 ±0.10                         | Thickness (mm): |
| Ground, protective bevel as needed | Edges:          |

Optical Properties

|                                                                                                                                                                 |                                     |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------|
| 40-20                                                                                                                                                           | Surface Quality:                    |
| Coating Specification:<br>Ravg >99% @ 850 - 1150nm, 0° Rs >99% @ 800 - 1150nm, 45° Rp >98.5% @ ~850 - 1100nm, 45°                                               |                                     |
| 0 ±30 fs² @ 800-1100 nm                                                                                                                                         | GDD Specification:                  |
| 800 - 1150                                                                                                                                                      | Wavelength Range (nm):              |
| λ/10                                                                                                                                                            | Surface Flatness (P-V):             |
| Ultrafast-Enhanced Silver                                                                                                                                       | Coating Type:                       |
| Ultrafast-Enhanced Silver (800-1150nm)                                                                                                                          | Coating:                            |
| Optical Grade Silicon                                                                                                                                           | Substrate: <input type="checkbox"/> |
| Damage Threshold, Reference: <input type="checkbox"/><br>0.35 J/cm² @ 1030nm, 200fs, 1 pulse (typical) 0.10 J/cm² @ 1030nm, 200fs, 100Hz, 1000 pulses (typical) |                                     |

Regulatory Compliance

|                      |                             |
|----------------------|-----------------------------|
| <a href="#">View</a> | Certificate of Conformance: |
|----------------------|-----------------------------|

## Product Details

- Silicon Substrate for Thermally Demanding Ultrafast Setups
- Ideal For Ti:Sapphire- and Yb-Based Ultrafast Laser Systems
- Designed For Ultrafast Pulse Reflection Where Low Dispersion is Critical
- < 30fs² GDD in Target Wavelength Ranges

TECHSPEC® Ultrafast-Enhanced Silver Coated Silicon Laser Mirrors combine a broadband enhanced-silver coating with low group delay dispersion (GDD) for ultrafast pulse applications. These mirrors are designed for systems where maintaining pulse fidelity is critical, and reflectivity and GDD are characterized across the specified wavelength range of 600 – 1000nm or 800 – 1150nm. These silicon substrate mirrors feature higher thermal conductivity than comparable [fused silica substrate mirrors](#), which helps evenly distribute absorbed heat in thermally demanding optical setups. TECHSPEC® Ultrafast-Enhanced Silver Coated Silicon Laser Mirrors are ideal for broadband ultrafast beam delivery where high reflectivity, controlled dispersion, and a thermally robust substrate are desired.