

TECHSPEC[®] 800 - 1200nm, 25mm Dia., Dichroic Shortpass Filter Kit (9 Filters)



Stock **#15-107** [CONTACT US](#)

-

1

+

€1.512^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€1.512,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Filters Included :

Cut-off Wavelengths: [800nm](#), [850nm](#), [900nm](#), [950nm](#), [1000nm](#), [1050nm](#), [1100nm](#), [1150nm](#), [1200nm](#)

Type:

Shortpass Filter

Number of Filters:

9

Physical & Mechanical Properties

	Diameter (mm):
25.00	
	Physical Durability:
Adhesion per MIL-PRF-13830B, Section C.4.5.12	
Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11	
Cleaning per MIL-C-48497A Section 4.5.4.2	

Environmental & Durability Factors

	Environmental Durability:
Humidity per ML-STD-810H, Section 507.6	
Temperature per ML-STD-810H, Section 501.7 and 502.7	

Regulatory Compliance

	Certificate of Conformance:
View	

Product Details

- Sharp Cut-Off Wavelength
- Broad Transmission and Reflection Ranges
- Available in a Range of Common Sizes

Our TECHSPEC® Dichroic Shortpass Filters are designed for a 45° angle of incidence. The rejected light is reflected at 90°, making these filters ideal for use in fluorescence applications or as spectral beamsplitters. The filters feature low polarization dependence, broad spectral ranges, and a precision fused silica substrate. TECHSPEC® Dichroic Shortpass Filters have a sharp cut-off wavelength and are available in a wide range of sizes for ease of system integration. These filters can be combined with TECHSPEC® Dichroic Longpass Filters to create custom bandpass filters.

Note: The chevron on the edge of the filter points towards surface S1 with the primary filter coating on which the light should be incident.

Technical Information

