

# Allied Vision Mako G-319 1/1.8" Color CMOS Camera

See More by [Allied Vision](#)



Allied Vision Mako Power over Ethernet (PoE) Cameras (Front)



Stock **#36-175** **2 In Stock**

[Similar Cameras](#)

-

1

+

€860<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €860,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

Product Downloads

## SPECIFICATIONS

| General                                                            |                             |
|--------------------------------------------------------------------|-----------------------------|
| Color Camera                                                       | Type:                       |
|                                                                    |                             |
| G-319C                                                             | Model Number:               |
| Allied Vision                                                      | Manufacturer:               |
|                                                                    |                             |
| Mako                                                               | Camera Series:              |
| Color                                                              | Spectrum:                   |
|                                                                    |                             |
| Physical & Mechanical Properties                                   |                             |
| 42.6 x 29.2 x 29.2 (excludes connectors and lens mount)            | Dimensions (mm):            |
|                                                                    |                             |
| 80                                                                 | Weight (g):                 |
| Full                                                               | Housing:                    |
|                                                                    |                             |
| Sensor                                                             |                             |
| 64MB                                                               | Image Buffer:               |
|                                                                    |                             |
| 1/1.8"                                                             | Sensor Format:              |
| 3.20                                                               | Resolution (Megapixels):    |
|                                                                    |                             |
| 37.50                                                              | Frame Rate (fps):           |
| 2,048 x 1,544                                                      | Pixels (H x V):             |
|                                                                    |                             |
| 3.45 x 3.45                                                        | Pixel Size, H x V (µm):     |
| 7.1 x 5.3                                                          | Sensing Area, H x V (mm):   |
|                                                                    |                             |
| Sony IMX265                                                        | Imaging Sensor:             |
| Progressive Scan CMOS                                              | Type of Sensor:             |
|                                                                    |                             |
| Global                                                             | Shutter Type:               |
| 8/12 bit                                                           | Pixel Depth:                |
|                                                                    |                             |
| Auto Exposure                                                      | Exposure Time:              |
| 72.7                                                               | Dynamic Range (dB):         |
|                                                                    |                             |
| GigE Vision V1.2, GenICam SFNC V1.2.1                              | Machine Vision Standard:    |
| Electrical                                                         |                             |
| 2.7 (12VDC External Power Supply)<br>3.1 (PoE)                     | Power Consumption (W):      |
|                                                                    |                             |
| Hardware & Interface Connectivity                                  |                             |
| GigE (PoE)                                                         | Interface:                  |
|                                                                    |                             |
| GigE, RJ45 with Screw Locks                                        | Connector:                  |
| Power over Ethernet (PoE), via GPIO, or with external power supply | Power Supply:               |
|                                                                    |                             |
| 1 opto-isolated input, 3 opto-isolated outputs                     | GPIOs:                      |
| Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)      | Synchronization:            |
|                                                                    |                             |
| Back Panel                                                         | Interface Port Orientation: |
| 8-pin Hirose (HR25)                                                | GPIO Connector Type:        |
|                                                                    |                             |
| Threading & Mounting                                               |                             |

|                                  |                         |
|----------------------------------|-------------------------|
| C-Mount                          | Mount:                  |
| 1/4-20 with Tripod Mount Adapter | Mounting Threads:       |
|                                  | <a href="#">#88-483</a> |

### Environmental & Durability Factors

|            |                             |
|------------|-----------------------------|
| +5 to +45  | Operating Temperature (°C): |
| -10 to +70 | Storage Temperature (°C):   |

### Regulatory Compliance

|                           |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
| <a href="#">View</a>      | Certificate of Conformance: |
| <a href="#">Compliant</a> | Reach 240:                  |

## PRODUCT DETAILS

- Compact, Robust Metal Housing
- One Optocoupled Input, Three Outputs
- Power over Ethernet for Increased Flexibility

Allied Vision Mako Power over Ethernet (PoE) Cameras are ideal digital replacements for analog cameras in a variety of applications, including robots, inspection, or logistics. Allied Vision Mako PoE Cameras feature a precision-aligned sensor to maximize image performance, in addition to a 64MB image buffer. To increase adaptability, Allied Vision Mako PoE Cameras also come equipped with multiple smart features, including the region of interest readout, programmable exposure and white balance, and easy bandwidth control. Allied Vision Mako Power over Ethernet (PoE) Cameras utilize a robust metal housing along with camera temperature monitoring to ensure maximum performance in a range of environments. These cameras are offered in both monochrome and color, with varying resolutions.

**Note:** GigE cable and power supply (if not using PoE) required for operation.