

[See all 58 Products in Family](#)

# Basler Ace acA4112-30um USB 3.0 Monochrome Camera

See More by [Basler](#)



Basler ace USB 3.0 Cameras (Front)



Stock **#37-223** **1 In Stock**

[Similar Cameras](#)

-

1

+

€3.510<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €3.510,00 each                |
| Need More?     | <a href="#">Request Quote</a> |

 Prices shown are exclusive of VAT/local taxes

Product Downloads

|                   |           |
|-------------------|-----------|
| Monochrome        | Spectrum: |
| General           |           |
| Monochrome Camera | Type:     |
| Model Number:     |           |

|                                                                                           |                             |
|-------------------------------------------------------------------------------------------|-----------------------------|
| acA4112-30um                                                                              |                             |
| Basler                                                                                    | Manufacturer:               |
| ace                                                                                       | Camera Series:              |
| Physical & Mechanical Properties                                                          |                             |
| 35.8 x 40 x 30 (excludes connectors and lens mount)                                       | Dimensions (mm):            |
| 80                                                                                        | Weight (g):                 |
| Full                                                                                      | Housing:                    |
| Sensor                                                                                    |                             |
| Not Specified                                                                             | Image Buffer:               |
| 1.1"                                                                                      | Sensor Format:              |
| 12.00                                                                                     | Resolution (Megapixels):    |
| 30.00                                                                                     | Frame Rate (fps):           |
| 4,096 x 3,000                                                                             | Pixels (H x V):             |
| 3.45 x 3.45                                                                               | Pixel Size, H x V (µm):     |
| 14.13 x 10.35                                                                             | Sensing Area, H x V (mm):   |
| Sony IMX253                                                                               | Imaging Sensor:             |
| Progressive Scan CMOS                                                                     | Type of Sensor:             |
| Global                                                                                    | Shutter Type:               |
| 10/12 bit                                                                                 | Pixel Depth:                |
| Programmable via camera API, hardware trigger                                             | Exposure Time:              |
| 72.8                                                                                      | Dynamic Range (dB):         |
| USB3 Vision v1.0                                                                          | Machine Vision Standard:    |
| Electrical                                                                                |                             |
| 3.6                                                                                       | Power Consumption (W):      |
| Hardware & Interface Connectivity                                                         |                             |
| USB 3.0                                                                                   | Interface:                  |
| USB 3.0, Micro-B with Screw Locks                                                         | Connector:                  |
| Power over USB                                                                            | Power Supply:               |
| 1 opto-coupled input line, 1 opto-coupled output line, 2 general purpose I/O (GPIO) lines | GPIOs:                      |
| Hardware Trigger (GPIO), Software Trigger, or Free-Run                                    | Synchronization:            |
| Back Panel                                                                                | Interface Port Orientation: |
| 6-pin Hirose (HR10)                                                                       | GPIO Connector Type:        |
| Threading & Mounting                                                                      |                             |
| C-Mount                                                                                   | Mount:                      |
| 1/4-20 with Tripod Mount Adapter <a href="#">#12-611</a>                                  | Mounting Threads:           |
| Environmental & Durability Factors                                                        |                             |
| 0 to +50                                                                                  | Operating Temperature (°C): |


|                           |                             |
|---------------------------|-----------------------------|
| Storage Temperature (°C): |                             |
| -20 to +80                |                             |
| Regulatory Compliance     |                             |
| Compliant                 | RoHS 2015:                  |
|                           |                             |
| View                      | Certificate of Conformance: |
|                           |                             |
| Compliant                 | Reach 235:                  |
|                           |                             |

## Product Details

- High Speed USB 3.0 Interface
- Ultra-Small Form Factor
- Fully USB3 Vision Compliant

Basler ace USB 3.0 Cameras are an ideal choice for analog camera users looking to upgrade to digital, or for FireWire or USB 2.0 users looking for faster data transfer rates. Basler ace USB 3.0 Cameras are fully USB3 Vision compliant and feature a small, 29 x29mm form factor that makes them easy drop-in replacements for many analog, FireWire, or USB 2.0 cameras. Additionally, these USB 3.0 cameras feature screw-locking USB 3.0 ports for increased ruggedness in demanding applications, such as factory floor use. All cameras include the Basler Pylon SDK software and driver.

## Technical Information



MT9P031 Sensor QE Curve