

[See all 49 Products in Family](#)

# Allied Vision Alvium G5-1240c, 1/1.7" 12.2MP C-Mount, 5GigE PoE Color Camera

See More by [Allied Vision](#)



Stock #23-632 **7 In Stock**

€870<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€870,00 each
Need More?	<a href="#">Request Quote</a>

! Prices shown are exclusive of VAT/local taxes

## Product Downloads

Color **Spectrum:**

## General

Color Camera **Type:**

Alvium G5-1240c **Model Number:**

Allied Vision **Manufacturer:**

Alvium G5

Camera Series:

## Physical & Mechanical Properties

60 × 29 × 29	Dimensions (mm):
100	Weight (g):
Full	Housing:

## Sensor

512KB	Image Buffer:
1/1.7"	Sensor Format:
12.20	Resolution (Megapixels):
41.00	Frame Rate (fps):
4,024 x 3,036	Pixels (H x V):
1.85 x 1.85	Pixel Size, H x V (µm):
7.44 x 6.61	Sensing Area, H x V (mm):
Sony IMX226	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/10 bit	Pixel Depth:
10 µs to 10 s	Exposure Time:
Not Specified	Dynamic Range (dB):
GigE Vision V2.2, GenICam V2.0	Machine Vision Standard:

## Electrical

External power: 6.1 W at 12 VDC   Power over Ethernet: 6.8 W	Power Consumption (W):
--	------------------------

## Hardware & Interface Connectivity

5GigE (PoE)	Interface:
5GigE, RJ45 with Screw Locks	Connector:
PoE, 12 to 24 VDC via GPIO, or with external power supply #23-581	Power Supply:
1 opto-isolated input, 1 opto-isolated output, 2 non-isolated GPIOs	GPIOs:
Hardware Trigger (GPIO) or Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
10-pin TFM	GPIO Connector Type:

## Threading & Mounting

C-Mount	Mount:
¼"-20 and M6 with Tripod Mount Adapter <a href="#">#14-156</a>	Mounting Threads:

## Environmental & Durability Factors

+5 to +60	Operating Temperature (°C):
-20 to +85	Storage Temperature (°C):

## Regulatory Compliance

[Compliant](#)

**RoHS 2015:**

[View](#)

**Certificate of Conformance:**

[Compliant](#)

**Reach 240:**

## Product Details

- 4.2 Times More Bandwidth than GigE
- Up to 24.6MP Resolution with Framrates up to 691 FPS
- Onboard Image Processing and Expansive Feature Sets

Allied Vision Avium G5 5GigE PoE Cameras feature a lightweight, compact form factor and combines the advantages of the established 5GigE Vision standard with the flexibility of the Avium platform. Powered by ALMUM® Technology, the sugar cube style camera delivers high image quality at a low power consumption. These cameras feature the latest industrial standard hardware and can easily be integrated into any USB3 Vision or GigE Vision system while ensuring long-term availability and reliability. With precision sensor alignment, enhanced cleanliness, fixed pattern noise correction, and defect pixel correction, resolutions up to 24.6MP and framerates up to 691 FPS are available. Allied Vision Avium G5 5GigE PoE Cameras feature a gigabit ethernet port on the back panel and are available in a variety of monochrome and color options with either C-Mount or S-Mount lens interfaces all in the compact sugar cube format.