

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Machine Vision Mounted Color Filters](#)

[See all 298 Products in Family](#)

SWIR M40.5 x 0.50

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit



Mounted Machine Vision Filters

1

€532⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€532,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

[EO Spec Sheet](#)

General

Type: Mounted Bandpass Filter

Physical & Mechanical Properties

Clear Aperture CA (mm): 35.5

Construction: Mounted in Black Anodized Ring

Outer Diameter (mm): 42.5

Optical Properties

Blocking Wavelength Range (nm): 900-1430, 2210-2300

Color: SWIR

Center Wavelength CWL (nm): 1,550.00

Full Width-Half Max FWHM (nm): 190.00

Minimum Transmission (%): ≥88

Threading & Mounting

Filter Thread: M40.5 x 0.50

Mount Thickness (mm): 5.2

Mount Thickness Including Threads (mm): 7

Regulatory Compliance

Certificate of Conformance: [View](#)

Reach 242: [Compliant](#)

Product Details

- Optimized for Use with Popular LEDs
- Multiple Mounting Sizes and Threads Available
- $\geq 85\%$ Transmission
- **TECHSPEC® High Performance Mounted Machine Vision Filters**

Mounted Machine Vision Filters are ideal for machine vision applications. Available in UV, VIS, and NIR wavelengths. They are designed with a Gaussian transmission curve. While they are compatible with many types of imaging lenses, these filters are ideal for wide fields of view due to their low angular dependency.

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

of common machine vision threads from M22 up to M105. Available in UV, VIS, and NIR wavelengths. They are designed with a Gaussian transmission curve. While they are compatible with many types of imaging lenses, these filters are ideal for wide fields of view due to their low angular dependency.


Related Products



Imaging Lenses



Machine Vision Filter Adapters



Machine Vision Lighting



High Performance Mounted Machine Vision Filters