

BWA-CAM UV BWA Etalon Optic Assembly, 325nm-425nm



Stock #89-716 NEW CONTACT US

-

1

+

€12.175<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €12.175,00 each               |
| Need More?     | <a href="#">Request Quote</a> |

!

Prices shown are exclusive of VAT/local taxes

Product Downloads

## SPECIFICATIONS

### General

BWA-CAM-325-425-R6-EO

Model Number:

### Physical & Mechanical Properties

91.0 x 85.0 x 78.0

Dimensions (mm):

### Optical Properties

325 - 425

Spectral Range:

### Regulatory Compliance

[View](#)

Certificate of Conformance:

## PRODUCT DETAILS

- Real-Time Analysis of Laser Beam Caustic, M<sup>2</sup>, Centroid, Ellipticity, and Astigmatism
- Compatible with CW and Pulsed Lasers with Single-Pulse Capability
- Ideal for Laser Development, Quality Control, and Optical System Monitoring
- Complies with ISO 11146 and ISO 13694

Haas Laser Technologies BWA-CAM M<sup>2</sup> Analyzer Cameras offer real-time M<sup>2</sup> measurement for continuous wave and pulsed lasers in UV, VIS, or IR wavelength configurations. Featuring a simple “one-button” calibration, this system is capable of delivering M<sup>2</sup> measurements from a single pulse, making it ideal for dynamic or single-shot laser systems. Engineered in compliance with ISO 11146 and ISO 13694 standards, the BWA-CAM provides precise evaluation of critical spatial beam parameters, including M<sup>2</sup>, beam profile, centroid, ellipticity, and astigmatism. Haas Laser Technologies BWA-CAM M<sup>2</sup> Analyzer Cameras enable users to detect optical system degradation early and optimize laser performance for maximum quality and process stability. The modular design of the BWA-CAM supports a broad range of laser wavelengths and application environments, while its high measurement accuracy and real-time data acquisition make it an essential tool for R&D, manufacturing, and laser system diagnostics.