

# Coherent® LabMax-Pro SSIM 1268881

See More by [Coherent®](#)



#35-302 Coherent® LabMax-Pro SSIM 1268881

Stock **#35-203** [CONTACT US](#)

-

1

+

€1.685<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €1.685,00 each                |
| Need More?     | <a href="#">Request Quote</a> |

**i** Prices shown are exclusive of VAT/local taxes

Product Downloads

| General                                                                                                         |                              |
|-----------------------------------------------------------------------------------------------------------------|------------------------------|
| 1268881                                                                                                         | Model Number:                |
| Power, Energy, and Beam Position                                                                                | Type:                        |
| ±1.0                                                                                                            | Calibration Uncertainty (%): |
| Max. Repetition Rate: 20,000Hz<br>Coherent® <a href="#">Thermopile Power Sensors</a> , <a href="#">Position</a> | Note:                        |

Sensing Thermopile Power Sensors, Laser Energy Sensors, or High Sensitivity Sensors Sold Separately

Physical & Mechanical Properties

|        |              |
|--------|--------------|
| 105.00 | Length (mm): |
| 105.00 | Width (mm):  |
| 0.3    | Weight (kg): |
| 32     | Depth (mm):  |

Optical Properties

|                                                     |             |
|-----------------------------------------------------|-------------|
| 0.1% Full Scale at 10Hz<br>0.2% Full Scale at 20kHz | Resolution: |
|-----------------------------------------------------|-------------|

Electrical

|                                |                           |
|--------------------------------|---------------------------|
| 0 to 1, 2, or 4 V (Selectable) | Analog Output:            |
| 625,000                        | Power Sampling Rate (Hz): |

Hardware & Interface Connectivity

|                                       |                     |
|---------------------------------------|---------------------|
| 90-260 VAC, 50/60 Hz AC Power Adapter | Power Supply:       |
| USB & RS232                           | Computer Interface: |

Environmental & Durability Factors

|            |                             |
|------------|-----------------------------|
| +5 to +40  | Operating Temperature (°C): |
| -20 to +70 | Storage Temperature (°C):   |

Regulatory Compliance

|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| View      | Certificate of Conformance: |

Product Details

- Coherent® Thermopile Power Sensors, Position Sensing Thermopile Sensors, Laser Energy Sensors, or High Sensitivity Sensors Sold Separately
- FieldMate Used to Measure Laser Power
- FieldMaxII Used to Measure Laser Power and Energy
- ISO 17025 Certified

Coherent® Laser Power and Energy Meters are designed to accurately measure and help tune the power or energy of continuous wave and pulsed lasers. The FieldMate, which features an analog needle with a large LCD display, is compatible with thermopile or optical sensors and is an economical solution for measuring laser power when advanced data analysis is not necessary. The FieldMaxII utilizes a large, backlit LCD screen and features a USB interface for computer connectivity. Coherent® Laser Power and Energy Meters feature FieldMaxII-TO, which is compatible with thermopile or optical sensors, while the FieldMaxII-TOP is compatible with thermopile, optical, or pyroelectric sensors. The LabMax is an all-in-one solution for measuring laser power or energy and is ideal for applications requiring advanced data analysis. The LabMax-TOP is compatible with thermopile, optical, or pyroelectric sensors. The LabMax Pro is the most advanced power and energy meter and is compatible with thermopile, optical, and pyroelectric sensors, as well as the PowerMaxPro high speed sensor technology. The LabMax Pro can provide advanced analysis up to 625kHz.