

Coherent® High-Sensitivity Thermopile Sensor PM3 1098336 | 2W Max Power

See More by [Coherent®](#)



Coherent® High-Sensitivity Thermopile Sensors

Stock **#12-403** **6 In Stock**

-

1

+

€1.170⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.170,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Model Number:
PM3 Coherent Part Number: 1098336

Type:
[Meter required](#)

Linearity (%):
±1

1	Calibration Uncertainty (%):
Air	Cooling Method:
2	Response Time (s):
Note: Includes a Removable 10mm ID Light Tube to Eliminate Stray Light	
Compatible Meters: #35-203 , #12-393 , #59-978 , #88-411 , #66-277 , #88-412	
Maximum Incident Energy Density: 50mJ/cm ² (10ns, 1064nm)	
Physical & Mechanical Properties	
19	Active Area Diameter (mm):
Optical Properties	
514	Calibration Wavelength (nm):
300 - 11000	Wavelength Range (nm):
0.3 - 11	Wavelength Range (µm):
Sensor	
Thermopile	Type of Sensor:
Electrical	
0.5	Maximum Incident Power Density (kW/cm ²):
500µW - 2W	Power Range:
2	Maximum Power (W):
50µW	Power Resolution:
Hardware & Interface Connectivity	
2	Length of Cable (m):
DB-25	Computer Interface:
Environmental & Durability Factors	
No	Thermally Stabilized:
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

PRODUCT DETAILS

- Broad Spectral Range with High Sensitivity and High Resolution
- Large Active Area Sensors up to 19mm in Diameter
- Flat Broadband Output with No Saturation above 1mW/cm²

Coherent® High-Sensitivity Thermopile Sensors are designed to have a broad spectral response to accommodate an array of lasers with different wavelengths. The large active area and high resolution of these thermopile sensors allows for accurate measurements of low-power lasers. A range of models are available to meet specific needs relating to thermal stability, background radiation, and air current effect. Coherent® High-Sensitivity Thermopile Sensors are designed to accurately measure the laser power of small laser diodes, HeNe lasers, and small ion lasers. Unique to this design, these sensors will not saturate when laser power exceeds 1mW/cm².