

Coherent® Thermopile Power Sensor 1098314 | 100mW - 30W, DB25

See More by [Coherent®](#)



Stock **#12-404** 3 In Stock

-

1

+

€1.370⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.370,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Model Number:

PM30
Coherent Part Number: 1098314

Type:

[Meter required](#)

Calibration Uncertainty (%):

±1

0.5 - 50	Long Pulse Joule Mode Range (J):
Air	Cooling Method:
0.6 @ 1064nm, 10ns	Maximum Incident Energy Density (J/cm²):
#35-203 , #12-393 , #59-978 , #88-411 , #66-277 , #88-412	
Compatible Meters:	

Physical & Mechanical Properties

19	Active Area Diameter (mm):
----	----------------------------

Optical Properties

10mW	Resolution:
514	Calibration Wavelength (nm):
190 - 11000	Wavelength Range (nm):
0.19 - 11	Wavelength Range (µm):

Sensor

Thermopile	Type of Sensor:
------------	-----------------

Electrical

50 (air-cooled)	Maximum Intermittent Power, <5min (W):
6	Maximum Incident Power Density (kW/cm²):
100mW - 30W	Power Range:

Hardware & Interface Connectivity

2.0	Length of Cable (m):
DB25	Computer Interface:

Regulatory Compliance

Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- Superior Damage Resistance
- Wide Dynamic Range
- ISO 17025 Certified

Coherent® Thermopile Power Sensors are ideal for measuring the average power of continuous wave lasers or pulsed laser energy. Thermopile sensors operate by absorbing and converting incident laser radiation into heat, which then flows to a heat sink. The temperature difference between the absorber and heat sink is converted into an electrical signal by a thermocouple junction. Coherent® Thermopile Power Sensors, unlike semiconductor sensors, do not saturate. Unlike semiconductor sensors, thermopile sensors feature high power capability and flat spectral response.