

[See all 78 Products in Family](#)

# Preloaded Norland Optical Adhesive NOA 1348 Dispensing Barrel (3cc)

See More by [Norland](#)



3cc Dispensing Barrel for NOA (NOA 60 shown as an example)



Stock #12-855 **1 In Stock**

€39.<sup>50</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-11	€39,50 each
Qty 12-19	€35,60 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

0.1 **Size (oz):**

1348 **Norland Number:**

**Shelf Life:**

4 months

Barrel **Type:**

**Typical Applications:**  
Low refractive index adhesive for bonding glass or plastic.

Contains 2g of adhesive **Note:**

### Optical Properties

1.348 @ 589nm **Index of Refraction ( $n_d$ ):**

315 - 450 **Absorption Range (nm):**

### Material Properties

Good **Glass Bonding:**

Good **Metal Bonding:**

Good **Plastic Bonding:**

160 **Viscosity (cps):**

Glass to Glass **Bonding Type:**

6 **Energy for Full Cure ( $J/cm^2$ ):**

### Environmental & Durability Factors

Soft Not Flexible **Durability:**

### Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **Reach 251:**

## Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

## Technical Information

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES	
Title	Description
<a href="#">Applying Adhesive</a>	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
<a href="#">Chemical Resistance of NOA</a>	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
<a href="#">Preventing Lens Separations with NOA</a>	Covers best practices to avoid adhesive failures when bonding optical elements.
<a href="#">Separating Lenses Bonded with NOA</a>	Covers how to unbond optical elements bonded with Norland Optical Adhesives.

