

[See all 78 Products in Family](#)

Preloaded Norland Optical Adhesive NOA 13685 Dispensing Barrel (3cc)

See More by [Norland](#)



3cc Dispensing Barrel for NOA (NOA 60 shown as an example)

Stock #12-852 **1 In Stock**

⊖ 1 ⊕ €27⁵⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-11 | €27,50 each |
| Qty 12-19 | €24,80 each |
| Need More? | Request Quote |

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

0.1 **Size (oz):**

13685 **Norland Number:**

4 months **Shelf Life:**

Type:

Barrel

Typical Applications:
Low viscosity adhesive for bonding glass or plastic.

Note:
Contains 2g of adhesive

Optical Properties

Index of Refraction (n_d):
1.3685 @589nm

Absorption Range (nm):
315 - 395

Material Properties

Glass Bonding:
Excellent

Metal Bonding:
Good

Plastic Bonding:
Fair

Viscosity (cps):
15 - 25

Bonding Type:
Glass to Glass

Energy for Full Cure (J/cm²):
6

Environmental & Durability Factors

Durability:
Soft & Flexible

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 251:
[Compliant](#)

Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

Technical Information

| NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES | |
|--|---|
| Title | Description |
| Applying Adhesive | Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles. |
| Chemical Resistance of NOA | Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents. |
| Preventing Lens Separations with NOA | Covers best practices to avoid adhesive failures when bonding optical elements. |
| Separating Lenses Bonded with NOA | Covers how to unbond optical elements bonded with Norland Optical Adhesives. |