

[See all 78 Products in Family](#)

# Preloaded Norland Optical Adhesive NOA 68 Dispensing Barrel (3cc)

See More by [Norland](#)



3cc Dispensing Barrel for NOA (NOA 60 shown as an example)

Stock #55-158 **7 In Stock**

⊖ 1 ⊕ €27<sup>50</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-11	€27,50 each
Qty 12-19	€24,80 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

## Product Downloads

## General

0.1 **Size (oz):**

68 **Norland Number:**

4 months **Shelf Life:**

**Type:**

Barrel

**Typical Applications:**  
High viscosity adhesive for plastics: acrylic polycarbonate and CAB.

**Note:**  
Contains 2g of adhesive

### Physical & Mechanical Properties

**Size (cc):**  
3.00

### Optical Properties

**Index of Refraction ( $n_d$ ):**  
1.54 @ 589nm

**Absorption Range (nm):**  
350 - 380

### Material Properties

**Glass Bonding:**  
Excellent

**Metal Bonding:**  
Good

**Plastic Bonding:**  
Excellent/Good

**Viscosity (cps):**  
5000

**Bonding Type:**  
Plastic to Plastic/Glass

**Energy for Full Cure ( $J/cm^2$ ):**  
4.5

### Environmental & Durability Factors

**Durability:**  
Flexible

### Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 251:**  
[Compliant](#)

## Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

## Technical Information

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES	
Title	Description
<a href="#">Applying Adhesive</a>	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
<a href="#">Chemical Resistance of NOA</a>	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
<a href="#">Preventing Lens Separations with NOA</a>	Covers best practices to avoid adhesive failures when bonding optical elements.
<a href="#">Separating Lenses Bonded with NOA</a>	Covers how to unbond optical elements bonded with Norland Optical Adhesives.

