

## Dual Bandpass VIS-NIR filter M25.5



Stock #74-534 NEW 1 In Stock

- 1 + €127.<sup>00</sup>

ADD TO CART

### Volume Pricing

Qty 1+	€127,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

**Full Width-Half Max FWHM Range (nm):**  
110nm, 375nm ±10 nm

### General

**Type:**  
Dual Bandpass Mounted Imaging Filter

**Model Number:**  
DB395/870-25.5

### Physical & Mechanical Properties

**Outer Diameter (mm):**  
27.5

2mm **Substrate Thickness (mm):**

## Optical Properties

AR **Coating:**

VIS-NIR **Color:**

40/20 **Surface Quality:**

≥90% **Transmission (%):**

375-425nm, 745-970nm **Transmission Wavelength (nm):**

## Threading & Mounting

M25.5 x 0.50 **Filter Thread:**

5.2 **Mount Thickness (mm):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Block and Transmit Desired Key VIS and NIR Spectral Bands with One Filter
- Remove The Need for Dual Sensor Setups
- Anti-Reflection Coating for Durability and Performance
- Various Mounting Thread Options Available

Multi-Band Machine Vision Bandpass Filters feature both double or triple bandpass options in one filter, allowing for greater flexibility in system design. These filters are designed with up to ≥90% transmission in the visible (VIS) or near-infrared (NIR) spectra with various wavelength range combinations available. Additionally, these filters are AR coated for optimal transmission and feature a hard-coated, single-substrate design with superior surface quality to maximize optical performance. Multi-Band Machine Vision Bandpass Filters ensure accurate color reproduction by blocking unwanted wavelengths, eliminating the need for dual-sensor imaging. These filters are ideal for surveillance applications such as, security and intelligent traffic management, as well as normalized difference vegetation index (NDVI) imaging applications.

**Note:** Other filter threads are available upon request.