

[See all 7 Products in Family](#)

## E Series 6mm 2/3" Format Fixed Focal Length Lens



E Series 6mm 2/3" Format Fixed Focal Length Lens



Stock #29-994 **NEW** [CONTACT US](#)

⊖ 1 ⊕ €259.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€259,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

**Product Family:**  
E Series

**Note:**  
It is recommended to use [C-Mount Camera Imaging Filters](#) when filters are required.

**Imaging Lens Type:**  
Fixed Focal Length Lens

## Physical & Mechanical Properties

Variable Iris Option:

41.01 Length (mm):

30.0 Maximum Diameter (mm):

30.0 Outer Diameter (mm):

1.85 Maximum Rear Protrusion (mm):

41.01 Maximum Length (mm):

## Optical Properties

76.7° Horizontal Field of View @ Max Sensor Format:

64.9° Horizontal Field of View, 1/1.8" Sensor:

58.5° Horizontal Field of View, 1/2" Sensor:

11.00 Maximum Image Circle (mm):

0.002 Numerical Aperture NA, Object Side:

8 (7) Number of Elements (Groups):

400 - 700 Wavelength Range (nm):

6.00 Focal Length FL (mm):

250 - ∞ Working Distance (mm):

f/4 - f/16 Aperture (f/#):

0.849 Back Focal Length BFL (mm):

N4 MgF<sub>2</sub> Coating:

11.65 Entrance Pupil Position (mm):

16.17 Object Space Principal Plane (mm):

6.91 Image Space Principal Plane (mm):

2.42 Maximum Distortion (%):

-11.23 Exit Pupil Position (mm):

VS Lens Wavelength Range:

VS Wavelength:

## Sensor

2/3" Optimized Sensor Format:

2/3" Maximum Sensor Format:

2.74 Pixel Size (μm):

## Threading & Mounting

N/A Filter Thread:

M30.5 x 0.5 (Male) Front Thread:

C-Mount Mount:

## Environmental & Durability Factors

-20 to +60 For questions regarding operating Storage Temperature (°C):

## Regulatory Compliance

Certificate of Conformance:

[View](#)

---

## Product Details

- Cost Effective Solution for Systems that Require Large Depth of Field
- Up to  $\frac{2}{3}$ " C-Mount Lens
- Ideal for Logistics and Barcode Scanning Applications

Edmund Optics E Series Fixed Focal Length Lenses provide an affordable fixed focal length imaging solution without compromising performance. These lenses are designed for logistics applications that need to identify product size and shape, read barcodes, and help find product locations. These systems often don't require lenses designed with more demanding specifications like large format sensor coverage and small pixels, which can be costly. Edmund Optics E Series Fixed Focal Length Lenses are a balance of performance and cost designed with a maximum format of  $2/3$ ". To maintain affordability in prototyping and mass production, the lens housings have been simplified by removing focusing mechanics. However, the focus can still be adjusted by threading the lenses into and out of the camera, then locked with a locking ring. These lenses maintain performance control with an adjustable iris ranging from  $f/4$  to  $f/16$ .

---

;