

[See all 2 Products in Family](#)

## E-Series Adjustable Rectangular Kinematic Mount



E-Series Adjustable Rectangular Kinematic Mount (#17-242)

Stock **#17-242** **5 In Stock**

⊖ 1 ⊕ €136<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	€136,00 each
Qty 10+	€129,30 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Adjustable - Tip-Tilt **Type:**

Rectangular **Type of Optics:**

2 **Number of Adjustment Screws:**

### Physical & Mechanical Properties

**Construction:**  
Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings

**Fine Tilt Angle (°):**  
±3.5

**Fine Tip Angle (°):**  
±3.5

**Adjustment Screw Pitch (mm):**  
0.25

**Min. Thickness of Compatible Optics (mm):**  
2

**Optical Axis Height (mm):**  
38.10

## Threading & Mounting

**Size of Compatible Optics (mm):**  
2.00 - 38.10

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 247:**  
[Compliant](#)

## Product Details

- Essential Mount for Experiments and OEM System
- Compatible with 3–38.1mm Rectangular Optics
- Compatible with 4-40mm Diameter Optics
- M6 x 0.25 (101.6 TPI) Adjustment Screws

E-Series Adjustable Size Kinematic Optical Mounts are ideal for integrating a range of round, rectangular, and square optical components. These kinematic mounts offer many features essential for applications in R&D, prototyping, and OEM system integration. Wide clear apertures enhance compatibility for both reflective optics like mirrors and transmissive optics like beamsplitters, filters, and cylinder lenses. The two M6 x 0.25 (101.6 TPI) adjustment screws provide smooth movement and can be driven by hand or by Allen key (2mm key size) for tip and tilt optical adjustment and alignment ( $\pm 3.5^\circ$ ). The adjustment screw knobs are removable to create a more compact form factor. E-Series Adjustable Size Kinematic Optical Mounts are compatible with M4, 8-32, and M6 x 1.0 hardware for increased mounting versatility and direct compatibility with [TECHSPEC® Metric Stainless Steel Mounting Posts](#) and [Pedestal Posts](#).

**Note:** #17-242 has an optical axis height of 38.1mm when mounting a 25.4mm optical component. #17-243 has a constant 38.1mm optical axis height when mounting any compatible sized optical component.