

High Resolution 1550nm Converter for CCD Cameras



Stock **#56-764** **3 In Stock**

-

1

+

€2.420⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€2.420,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

Physical & Mechanical Properties

46 Diameter x 97 L

Dimensions (mm):

210.00

Weight (g):

Active Area (mm):

27.5

Optical Properties

-1.0 Barrel	Distortion (%):
12 lp/mm over active area 40 lp/mm at Sensor focal plane	Resolution:

1495 - 1595 790 - 840, 870 - 1070, 1550 Peaks 950 - 1075 Converted IR Output	Spectral Response (nm):
--	-------------------------

1 W/cm ²	Damage Threshold, By Design: ☐
---------------------	---

Sensor

1/2"	Sensor Format:
------	----------------

Electrical

Analog: 30 - 40 Digital: 48, 68 (12 bit, 16 bit)	Dynamic Range (A):
---	--------------------

Threading & Mounting

M42 x 1.0 to Lens, C-Mount to Camera	Mount:
--------------------------------------	--------

Environmental & Durability Factors

-10 to +40	Operating Temperature (°C):
------------	-----------------------------

Regulatory Compliance

Compliant	Reach 191:
-----------	------------

Compliant	RoHS 2015:
-----------	------------

View	Certificate of Conformance:
------	-----------------------------

PRODUCT DETAILS

- Converter Extends Standard CCD Cameras into IR (1495 - 1595nm)
- Device for Imaging or Alignment Applications

High Resolution 1550nm Converter for CCD Cameras are a low cost alternative to expensive IR viewers. When attached to a monochrome camera with typical visible spectral response characteristics, it creates an imaging system with extended sensitivity into the NIR region. Conventional silicon based CCD cameras are predominantly sensitive around 850nm. Aproprietary phosphor coating (using patented AST technology) on both the Converter's lens system and 1550nm-camera's sensor converts the 1495 - 1595nm band to Si-based CCD detectable wavelengths without fade or lag.

With an imaging lens attached to the Converter, it acts as a 1:1 relay lens for 1/2" sensor cameras, simultaneously relaying high resolution, low distortion, uniform NIR images while converting the images to an Si detector wavelength. A focus ring at the rear of the Converter allows adjustment for wavelength-focus variation and focus optimization onto the camera. Large Format lenses (designed for sensors >28mm) are recommended to maintain highest resolution, in order to fill the Converter's active area and maximum light throughput.

Without an imaging lens (as shown in photo), the Converter is also useful for beam alignment as the phosphor coating allows visualization of any 1550nm beam on its input window. The Converter features a large aperture window that is anti-reflection coated to ensure maximum image resolution is transferred. Increased sensitivity for beam profiling and telecommunication applications can be obtained by utilizing the IR Converter together with the 1550nm camera. Other applications include surveillance and inspection.

Note: Phosphor coating is partially transmissive outside the optimized coating band (into the visible). For viewing objects in the visible-NIR spectrum simultaneously with 1550-NIR wavelengths, an illumination source with NIR output is recommended for use with the 1550nm camera, but especially for the Converter (since the optical system significantly reduces light throughput).