

[All Products](#) / [Lasers](#) / [Laser Safety](#)
/ [Laser Safety Glasses and Goggles](#)

[See all 110 Products in Family](#)

LS09 Adjustable Glasses

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit




Stock #12-738 **2 In Stock**

- 1 +

€234^{,00}

ADD TO CART

Image represents frame style only. Filter color will vary by product specification.



Volume Pricing	
Qty 1-5	€234,00 each
Qty 6-10	€210,60 each
Qty 11-25	€187,20 each
Need More?	Request Quote

Product Downloads



Curve:pdf



EO Spec Sheet



[Download All](#)

Prices shown are exclusive of VAT/local taxes

General

Style: Adjustable
Temples Wrap Around

EN 207/208 Ratings: D LB6 + R LB4 @ 180-315nm, DR LB4 @ 315-400nm, DIR LB1 @ 700-770nm, DIR LB2 @ 770-820nm, DIR LB3 @ 820-865nm, DIR LB4 @ 865-940nm, DIRM LB5 @ 940-1,064, DIRM LB4 @ 1,064-1,400nm, DI LB2 @ 1,400-1,850nm, DI LB1 @ 1,840-1,950nm

Filter Material: Polymer

Filter: LS09

Optical Properties

Optical Density OD (Average): >6 @ 190 - 450nm
>1 @ 700 - 770nm
>2 @ 770 - 1840nm
>3 @ 820 - 1720nm
>4 @ 870 - 1600nm
>5 @ 940 - 1070nm
>1 @ 1840 - 1950nm

Color: Green

Regulatory Compliance

RoHS 2015: **Compliant**

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Product Details

- CE Certified Laser Radiation Protection
- Designs for Ultraviolet, Visible, and Infrared Lasers
- Available in Eight Styles, Detailed Below

Laser Safety Glasses and Goggles feature high optical density at their specified wavelength range to protect against laser radiation. The durable lenses are molded with laser-protective absorptive dyes, causing accidental scratches to have no effect on their performance. Designs that protect against ultraviolet, visible, and infrared lasers are available. All Laser Safety Eyewear products are CE certified and come with a hard case, neck cord, and microfiber cloth.

Laser Safety Eyewear are available in eight styles:

Laser Safety Goggles: Fit over prescription glasses and are vented to prevent fogging, with a standard "lab goggle" shape.

Fit Over Rx Glasses: Fit over prescription glasses and have side-shields for a wide field of view.

Adjustable Temples, Wrap Around Frame Glasses: Feature a wrap around design with adjustable temple lengths and angle.

Adjustable Bridge, Wrap Around Frame Glasses: Feature a wrap around design with an adjustable bridge and comfort fit temples.

Vented Fit Over: Feature a more modern, vented design, meant to be worn over perscription lenses.

Vented, Adjustable Temples: Feature a more modern, vented design, with adjustable temples for increased comfort for long term use.

1 + 1 Flip Up: Features two different laser safety filters, one in the base frame and one in the flip up attachment. Ideal when working with more than one laser with largely different wavelengths.

Rx Flip Up: Features an empty base frame, allowing for the insertion of perscription lenses, with a laser safety filter in the flip up attachment.

XL Fit Over Rx : Features a larger frame size to fit over larger Rx glasses.

Warning: Because of the potential for eye damage, the degree of protection required in each circumstance should be determined by the Laser Safety Officer, the industrial hygienist, or the individual responsible for the safety program.

Frequently Purchased Together



#55-292 - Laser Detection Card IR
€108,00

Qty



#48-506 - 10° Diffusing Angle
25mm Dia., Fused Silica
Holographic Diffuser
€499,00

Qty



#48-509 - 25° Diffusing Angle
25mm Dia., Fused Silica
Holographic Diffuser
€499,00

Qty



#48-513 - 0.5° Diffusing Angle
50mm Dia., Fused Silica
Holographic Diffuser
€820,00

Qty

Resources

Media Type

- Video
- Glossary
- Application Note

VIDEO

Beam Combining for Increased Power

GLOSSARY

Pockels Cell

APPLICATION NOTE

Beam Quality and Strehl Ratio

FAQ

Scientific Paper

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

▶ VIDEO

Aligning
Mount for
AdiOptica
Beamshapers

[View More](#)