

Coherent® Beam Position Thermopile Power Sensors 1168340 | 10mW-10W

See More by [Coherent®](#)



Stock #68-628 5 In Stock

-

1

+

€1.805⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.805,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
LM-10 Coherent Part Number: 1168340	
Model Number:	
Meterless	
Type:	
±1	
Linearity (%):	
±2	
Calibration Uncertainty (%):	

0.5 - 10	Long Pulse Joule Mode Range (J):
±3	Long Pulse Joule Mode Accuracy (%):
Air	Cooling Method:
600mJ/cm² (10ns, 1064nm)	Maximum Incident Energy Density:

Physical & Mechanical Properties

16	Active Area Diameter (mm):
----	----------------------------

Optical Properties

10,600	Calibration Wavelength (nm):
0.25 - 10.6	Wavelength Range (µm):

Sensor

Quad Element Thermopile	Type of Sensor:
-------------------------	-----------------

Electrical

±1.5	Spectral Compensation Accuracy (%):
10	Maximum Incident Beam Power (W):
6	Maximum Incident Power Density (kW/cm²):
10mW - 10W	Power Range:
10	Minimum Power (mW):

Hardware & Interface Connectivity

2.5	Length of Cable (m):
USB	Computer Interface:

Regulatory Compliance

Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- Thermopile Detector Element for High Power Measurements
- Measure Beam Position on Detector Surface
- ISO 17025 Certified

Coherent® Beam Position Sensing Thermopile Power Sensors are all-purpose sensors designed to measure the average power or energy of a wide variety of continuous wave or pulsed lasers. Coherent Beam Position Sensing Thermopile Power Sensors utilize a quadrant thermopile detector disk to sense the position of the laser beam on the detector surface while measuring the laser power. Coherent thermopile sensors can operate across a wide range of input powers, and do not saturate.

Note: The LM-20 is designed for embedded use and must be mounted on a heat sink.