

White, Low-Angle Square Light FPQ3-96SW

See More by [CCS](#)



Stock **#21-810** [CONTACT US](#)

-

1

+

€1.630⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.630,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

FPQ3-96SW

Model Number:

LED Illuminator

Type of Illumination:

CCS	Manufacturer:
Low-Angle Square Light	Geometry:
Constant	Illumination Mode:
Physical & Mechanical Properties	
W 96 mm x D 96 mm x H 30 mm	Dimensions (mm):
170	Weight (g):
Optical Properties	
White	Color:
Electrical	
25	Power Consumption (W):
Hardware & Interface Connectivity	
24	Input Voltage (V):
Power Supply: Power Supply Required and Sold Separately. USA: #73-491 Europe: #73-491 Japan: #89-513 Korea: #33-773 China: #73-491	
Environmental & Durability Factors	
6000	Color Temperature (K):
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

PRODUCT DETAILS

- Improved Inspection of Rectangular and Square Objects vs. Ring Lights
- Low-Angle Lighting from Four Directions
- Ideal for Inspection of Food Packaging and PCB's

CCS Low-Angle Square LED Illuminators provide uniform diffuse illumination from a low angle in four directions. This low-angle square design helps to prevent glare and enables the detection of outlines and corners which is difficult to achieve with traditional ring lights. These lights feature mounting holes along the top and sides, allowing for flexibility with system installation. CCS Low-Angle Square LED Illuminators are ideal for embossed character recognition and inspection of square parts such as food packaging, circuit boards (PCB's), and print patterns.

Note: Power supply [#66-855](#) is required and sold separately.

TECHNICAL INFORMATION

Imaging Examples for the FPQ3-100X50 Light Unit

Illumination from a low angle clearly highlights the outline of workpieces.

■ **Conceptual Image for Illumination**
With uniform and diffused light at a low angle from four directions of the workpiece, the corners stand out.

■ **Workpiece Image: PC memory boards**

■ **FPQ2-120SW**

The connector pins are not clearly imaged because the distance between the emitting surface and the workpiece is large. Also, the whole surface of the workpiece is not uniformly illuminated.

■ **FPQ3-100X50SW**

The connector pins are clearly imaged because the distance between the emitting surface and the workpiece is short. Also, the whole surface of the workpiece is uniformly illuminated.