


[See all 16 Products in Family](#)

Low Noise Variable Voltage Amplifier



#90-634 Low Noise Variable Voltage Amplifier

Stock #90-634 NEW **1 In Stock**

⊖ 1 ⊕ €2.590⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€2.590,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Lower: DC/1.5
Upper: 10

Cut-Off Frequency (Hz):

General

Yes

Remote Control:

Includes:
LEMO® 3-pin connector
Datasheet

Note:

Electrical

Voltage Noise, High Gain (V/Hz^{1/2}):
7 x 10⁻¹⁰

Gain (dB):
40/60/80/100 (Switchable)

Input Impedance (kΩ):
1000

Hardware & Interface Connectivity

Output Voltage (V):
±10 V (@ 100 kΩ Load)

Power Supply:
Power Supply Required and Sold Separately.
USA: [#59-180](#)
Europe: [#59-180](#)
Japan: Not Available
Korea: Not Available
China: [#59-180](#)

Output Type:
50 Ω, BNC

Input Type:
1 MΩ, BNC

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Product Details

- High-Precision, Low-Frequency Signal Amplification with Constant Bandwidth Performance
- Low DC Offset Drift for Long-Term Measurement Stability
- AC/DC Coupling Options

Low-Frequency Voltage Amplifiers provide variable amplification of DC to 100kHz signals, allowing precise control over signal gain in sensitive measurement applications. Their low-noise design and wide gain range preserve signal fidelity across amplification settings, ensuring accurate voltage measurements even at high gain. By maintaining stable performance with minimal DC offset drift, these amplifiers improve measurement clarity, repeatability, and reliability in demanding laboratory and industrial settings. Low-Frequency Voltage Amplifiers feature switchable AC/DC coupling and remote control capability, providing flexibility for integration into automated systems or standalone setups. These amplifiers are ideal for sensor readout, low-level signal detection, and precise data acquisition across a wide range of scientific and engineering applications.

Note: Power supply sold separately. Please see specifications for more details.