

[See all 36 Products in Family](#)

# LUCID Vision Labs™ Atlas ATP081S-MC, Sony IMX546, 8.1MP, IP67 Monochrome Camera

See More by [LUCID Vision Labs™](#)



Stock **#23-963** **1 In Stock**

-

1

+

€1.360<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €1.360,00 each                |
| Need More?     | <a href="#">Request Quote</a> |

 Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

Product Downloads

|                   |               |
|-------------------|---------------|
| Monochrome        | Spectrum:     |
| General           |               |
| Monochrome Camera | Type:         |
| ATP081S-MC        | Model Number: |
| Manufacturer:     |               |

|                                                                                 |                             |
|---------------------------------------------------------------------------------|-----------------------------|
| Lucid Vision Labs                                                               |                             |
| Atlas IP67                                                                      | Camera Series:              |
| Physical & Mechanical Properties                                                |                             |
| 60 x60 x65                                                                      | Dimensions (mm):            |
| 340                                                                             | Weight (g):                 |
| Full                                                                            | Housing:                    |
| Sensor                                                                          |                             |
| 380MB                                                                           | Image Buffer:               |
| 2/3"                                                                            | Sensor Format:              |
| 8.10                                                                            | Resolution (Megapixels):    |
| 68.80                                                                           | Frame Rate (fps):           |
| 2,840 x2,840                                                                    | Pixels (H x V):             |
| 2.74 x2.74                                                                      | Pixel Size, H x V (µm):     |
| 7.78 x7.78                                                                      | Sensing Area, H x V (mm):   |
| Sony IMX546                                                                     | Imaging Sensor:             |
| Progressive Scan CMOS                                                           | Type of Sensor:             |
| Global                                                                          | Shutter Type:               |
| 8/10/12/16 Bit                                                                  | Pixel Depth:                |
| 8 µs to 10 s (Normal) / 2.31 µs to 2.47 µs (Short Mode)                         | Exposure Time:              |
| Not Specified                                                                   | Dynamic Range (dB):         |
| GigE Vision v2.0                                                                | Machine Vision Standard:    |
| Electrical                                                                      |                             |
| 8W via PoE, 7W when powered externally                                          | Power Consumption (W):      |
| Hardware & Interface Connectivity                                               |                             |
| 5GigE (PoE)                                                                     | Interface:                  |
| 5GigE, M12                                                                      | Connector:                  |
| PoE (IEEE 802.3af), or 12-24 VDC external                                       | Power Supply:               |
| 1 opto-isolated input, 1 opto-isolated out, 2 non-isolated bi-directional ports | GPIOs:                      |
| Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)                   | Synchronization:            |
| Back Panel                                                                      | Interface Port Orientation: |
| 8 pin M8 connector                                                              | GPIO Connector Type:        |
| Threading & Mounting                                                            |                             |
| C-Mount                                                                         | Mount:                      |
| Environmental & Durability Factors                                              |                             |
| -20 to 55                                                                       | Operating Temperature (°C): |
| -30 to 60                                                                       | Storage Temperature (°C):   |
| Regulatory Compliance                                                           |                             |

## Product Details

- IP67 Rated for Protection from Water Ingress, Dust and Dirt
- 5Gbase-T (5GigE) Ethernet Interface
- Supports Power over Ethernet (PoE), Simplifying Integration

LUCID Vision Labs Atlas IP67 5GigE Cameras are water ingress protected, industrial cameras designed for imaging applications requiring high bandwidth and performance in rugged environments. These cameras support the 5Gbase-T (5GigE) Ethernet interface and are Power over Ethernet (PoE), capable of 600 MB/s data transfer rates which allow for high resolution and frame rates. LUCID Vision Labs Atlas IP67 5GigE Cameras feature a C-mount and Active Sensor alignment for superior optical performance. These cameras offer a perfect balance of fast frame rates, compact size, industrial ruggedization, and an excellent price-performance ratio.