

[See all 37 Products in Family](#)

# LUCID Vision Labs™ Atlas ATP200S-CC, Sony IMX183, 20MP, IP67 Color Camera

See More by [LUCID Vision Labs™](#)



Stock #23-974 **1 In Stock**

⊖ 1 ⊕ €1.185<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€1.185,00 each
Need More?	<a href="#">Request Quote</a>

⚠ Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

## Product Downloads

Color	
	<b>Spectrum:</b>
General	
	<b>Type:</b>
Color Camera	
	<b>Model Number:</b>
ATP200S-CC	
	<b>Manufacturer:</b>

## Physical & Mechanical Properties

60 x 60 x 65 **Dimensions (mm):**

340 **Weight (g):**

Full **Housing:**

## Sensor

380MB **Image Buffer:**

1" **Sensor Format:**

20.00 **Resolution (Megapixels):**

17.90 **Frame Rate (fps):**

5,472 x 3,648 **Pixels (H x V):**

2.4 x 2.4 **Pixel Size, H x V (µm):**

13.13 x 8.75 **Sensing Area, H x V (mm):**

Sony IMX183 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Rolling **Shutter Type:**

12 bit **Pixel Depth:**

122.18 µs to 10 s **Exposure Time:**

Not Specified **Dynamic Range (dB):**

GigE Vision v2.0 **Machine Vision Standard:**

## Electrical

8W via PoE, 7W when powered externally **Power Consumption (W):**

## Hardware & Interface Connectivity

5GigE (PoE) **Interface:**

5GigE, M12 **Connector:**

PoE (IEEE 802.3af), or 12-24 VDC external **Power Supply:**

1 opto-isolated input, 1 opto-isolated out, 2 non-isolated bi-directional ports **GPIOs:**

Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588) **Synchronization:**

Back Panel **Interface Port Orientation:**

8 pin M8 connector **GPIO Connector Type:**

## Threading & Mounting

C-Mount **Mount:**

## Environmental & Durability Factors

-20 to 55 **Operating Temperature (°C):**

-30 to 60 **Storage Temperature (°C):**

## Regulatory Compliance

## Product Details

- IP67 Rated for Protection from Water Ingress, Dust and Dirt
- 5Gbase-T (5GigE) Ethernet Interface
- Supports Power over Ethernet (PoE), Simplifying Integration

LUCID Vision Labs Atlas IP67 5GigE Cameras are water ingress protected, industrial cameras designed for imaging applications requiring high bandwidth and performance in rugged environments. These cameras support the 5Gbase-T (5GigE) Ethernet interface and are Power over Ethernet (PoE), capable of 600 MB/s data transfer rates which allow for high resolution and frame rates. LUCID Vision Labs Atlas IP67 5GigE Cameras feature a C-mount and Active Sensor alignment for superior optical performance. These cameras offer a perfect balance of fast frame rates, compact size, industrial ruggedization, and an excellent price-performance ratio.

---

;