

[See all 33 Products in Family](#)

# M2590, 1" NIR, Teledyne DALSA Genie Nano GigE PoE Camera

See More by [Teledyne DALSA](#)



Teledyne DALSA Genie™ Nano GigE Cameras



Stock #14-677 **2 In Stock**

⊖ 1 ⊕ €1.140<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€1.140,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

NIR	<b>Spectrum:</b>
<b>General</b>	
NIR Camera	<b>Type:</b>
G3-GM12-M2590	<b>Model Number:</b>

Teledyne DALSA  
Genie Nano-1GigE

**Manufacturer:**  
**Camera Series:**

## Physical & Mechanical Properties

**Dimensions (mm):**  
40.6 x 29.0 x 44.0 (includes connectors and lens mount)

**Weight (g):**  
46

**Housing:**  
Full

## Sensor

**Image Buffer:**  
90MB

**Sensor Format:**  
1"

**Resolution (Megapixels):**  
5.30

**Frame Rate (fps):**  
22.70

**Frame Rate - Burst Mode (fps):**  
51.00

**Pixels (H x V):**  
2,592 x 2,048

**Pixel Size, H x V (µm):**  
4.8 x 4.8

**Sensing Area, H x V (mm):**  
12.44 x 9.83

**Imaging Sensor:**  
ON Semi PYTHON 5000

**Type of Sensor:**  
Progressive Scan CMOS

**Shutter Type:**  
Global

**Pixel Depth:**  
8/10 bit

**Exposure Time:**  
Programmable or via external trigger

**Dynamic Range (dB):**  
62.1

**Machine Vision Standard:**  
GigE Vision v1.2

## Electrical

**Power Consumption (W):**  
3.6 - 4.6 (12VDC External Power Supply)  
4.0 - 4.9 (PoE)

## Hardware & Interface Connectivity

**Interface:**  
GigE (PoE)

**Connector:**  
GigE, RJ45 with Screw Locks

**Power Supply:**  
Power over Ethernet (PoE) or via GPIO

**GPIOs:**  
2 digital input, 2 digital output

**Synchronization:**  
Hardware Trigger (GPIO), Software Trigger, Free-Run, or PTP (IEEE 1588)

**Interface Port Orientation:**  
Back Panel

**GPIO Connector Type:**  
10-pin Samtec

## Threading & Mounting

**Mount:**  
C-Mount

**Mounting Threads:**  
1/4-20 with Tripod Mount Adapter [#34-966](#)

## Environmental & Durability Factors

**Operating Temperature (°C):**

-20 to +60

Storage Temperature (°C):

-40 to +80

---

## Regulatory Compliance

[View](#)

Certificate of Conformance:

---

## Product Details

- TurboDrive™ Technology Achieve Frame Rate up to 800 fps
- Compact, Lightweight, Robust All Metal Body
- Global Electronic Shutter with Exposure Control and Advanced Feature Set



Teledyne  
Authorized  
Distributor

Teledyne DALSA Genie™ Nano GigE Cameras are available in a range of Sony Pregius and On Semiconductor CMOS sensors. These GigE PoE cameras provide high speed, low noise, and global electronic shutters. The proprietary TurboDrive™ technology allows the Genie™ Nano to exceed standard frame rates, delivering up to 800 fps while retaining full image quality. These cameras come with a host of advanced feature set such as multi ROI windows and Burst Acquisition, which utilizes onboard memory buffer to achieve even faster frame rates.\* Teledyne DALSA Genie™ Nano GigE Cameras are packaged in compact and robust all metal housing, making them ideal for electronics inspection, industrial metrology, and Intelligent Traffic Systems (ITS) applications.

**Note:** Frame rates achievable through TurboDrive™ or Burst Acquisition could vary with factors such as image quality and resolution.

**Sapera LT** is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sapera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sapera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 Vision™.