

# MicroBrite 150mm White Line Light



Stock #74-227 NEW **1 In Stock**

- 1 + €895<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€895,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

## General

LED Illuminator	<b>Type of Illumination:</b>
Compatible with #18-645 external controller	<b>Note:</b>
Advanced Illumination	<b>Manufacturer:</b>
Line Light	<b>Geometry:</b>
	<b>Illumination Mode:</b>

Constant

## Physical & Mechanical Properties

150.00 **Length (mm):**

174.5 L x 152.4 W x 20.1 D **Dimensions (mm):**

762 **Weight (g):**

## Optical Properties

White **Color:**

0.5-23 **Working Distance (inches):**

## Hardware & Interface Connectivity

Flying Leads **Connector:**

24VDC, 1.5A **Operating Voltage (V):**

**Power Supply:**  
Power Supply Required and Sold Separately.  
USA: [#66-855](#)  
Europe: [#66-855](#)  
Japan: [#89-513](#)  
Korea: [#33-773](#)  
China: [#66-855](#)

## Threading & Mounting

M4 Mounting Screws **Mount:**

## Environmental & Durability Factors

0 °C to 35 °C **Operating Temperature (°C):**

## Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **Reach 247:**

## Product Details

- Ideal For Line Scan Applications
- High Power LEDs in White, Red, and Blue
- Compact Form Factor for Easy Integration

The Advanced Illumination Microbrite™ Line Lights offer a compact solution for line scan applications. These lights are designed with a high intensity illumination profile and high thermal efficiency, enabling a long lifespan even with continuous operation. These illuminators feature an M4 mounting channel for ease of integration and are available in white, blue, and red wavelengths. The Advanced Illumination Microbrite™ Line Lights are ideal for line scan applications such as high speed inspection of materials including textiles, paper, or plastics and inspection of solar panels or LCDs.

[3D-Printable Mount Files](#)



Bar or Line Light Configuration

[Download Now](#)

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to 1/4-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



[Application Note](#)

[Illumination Mounts for Machine Vision Applications](#)

[Read](#)



[Video](#)

[Assembly of 3D Printed Mounts for Common Illumination Geometries](#)

[Watch](#)