

[See all 48 Products in Family](#)

Norland Optical Adhesive NOA 78, 100g Bottle

See More by [Norland](#)



Norland Optical Adhesive NOA 78, 100g Bottle

Stock **#17-348** **5 In Stock**

⊖ 1 ⊕ €123.⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-4 | €123,00 each |
| Qty 5-11 | €110,70 each |
| Qty 12+ | €105,20 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

3.52 **Size (oz):**

78 **Norland Number:**

4 months **Shelf Life:**

Bottle **Type:**

Typical Applications:
Bonding polarized film, cellulose acetate butyrate, glass, and plastics

UVMS **Cure:**

Optical Properties

1.50 @ 589nm **Index of Refraction (n_d):**

320 - 450 **Absorption Range (nm):**

Material Properties

Excellent **Glass Bonding:**

Good **Metal Bonding:**

Excellent **Plastic Bonding:**

8000 - 11000 **Viscosity (cps):**

Plastic to Plastic/Glass **Bonding Type:**

3.5 (Long Wave UV) 7 (Visible) **Energy for Full Cure (J/cm^2):**

Environmental & Durability Factors

Soft & Resilient **Durability:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 253:**

Product Details

- Excellent Optical Qualities
- Adhesives for Glass, Metal, and Plastic Bonding
- Cure Quickly when Exposed to UV Light
- [Preloaded Norland Optical Adhesive Syringes](#) Also Available

Norland Optical Adhesives are clear, solvent-free optical adhesives designed to fully cure in only minutes when exposed to ultraviolet light. These adhesives are used in precision alignment or positioning applications that require a robust and resilient bond. Norland Optical Adhesives feature a variety of bonding types, including but not limited to glass to glass, glass to glass/metal, and plastic to plastic/glass. To use Norland Optical Adhesives, apply the adhesive to the optical surface, position the components, and use a [UV light source](#) to set the components in place. Since the adhesive will not cure until exposed to UV light, time can be taken during the positioning process to perfect product alignment.

Technical Information

| NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES | |
|------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Title | Description |
| Applying Adhesive | Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles. |
| Chemical Resistance of NOA | Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents. |
| Preventing Lens Separations with NOA | Covers best practices to avoid adhesive failures when bonding optical elements. |
| Separating Lenses Bonded with NOA | Covers how to unbond optical elements bonded with Norland Optical Adhesives. |

