

Pulse 1.2 MP, Basler PowerPack Microscopy Camera



Basler PowerPack Pulse Microscopy Camera



Stock **#34-706** CLEARANCE 3-4 DAYS

-

1

+

€585⁰⁰

ADD TO CART

Qty 1+
€585,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Color Mcroscopy Camera

Type:

Basler	Manufacturer:
Accessories include a CS-Mount to C-Mount adapter ring and a USB3 cable	
Pulse	Camera Family:
Pulse 1.2 MP	Model Number:
Physical & Mechanical Properties	
38.8 Dia. x 28.64 Length (includes connectors and lens mount)	Dimensions (mm):
60	Weight (g):
Full	Housing:
Sensor	
Not Specified	Image Buffer:
ON Semi AR0134	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Type of Shutter:
1/3"	Camera Sensor Format:
1.20	Resolution (MegaPixels):
1,280 x 960	Pixels (H x V):
3.75 x 3.75	Pixel Size, H x V (µm):
4.8 x 3.6	Sensing Area, H x V (mm):
54.00	Frame Rate (fps):
Manual and Automatic	Exposure Time:
64.00	Dynamic Range (dB):
USB3 Vision v1.0	Machine Vision Standard:
Electrical	
Not Specified	Power Consumption (W):
Hardware & Interface Connectivity	
USB 3.0	Video Output:
USB 3.0, Micro-B	Connector:
Power over USB	Power Supply:
N/A	GPIOs:
Software Trigger or Free-Run	Synchronization:
Side Panel	Interface Port Orientation:
None	GPIO Connector Type:
Threading & Mounting	
¼-20 (Integrated into Housing)	Mounting Threads:
C/CS-Mbunt	Mount:
Environmental & Durability Factors	
	Operating Temperature (°C):

0 to +50	Storage Temperature (°C):
-20 to +80	

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

PRODUCT DETAILS

- High Performance Cameras Featuring State-of-the-Art CMOS Sensors
- Professional Software for Image Acquisition and Analysis Included
- Unique Advanced Image Enhancement and Color Adjustment Technology

Basler PowerPack Microscopy Cameras are available in various configurations designed for efficiency and performance. To facilitate system integration, these cameras have been designed with USB 3.0 connectivity with USB 2.0 backwards compatibility, as well as a small and compact form factor. The Pulse models utilize the industry established ON Semiconductor Aptina sensors, offering accurate reproducible results for a broad range of applications. The Ace model makes use of the SONY Pregius sensor which features low noise and large dynamic range. Basler PowerPack Microscopy Cameras are ideal for applications that require high frame rates for smooth live viewing, fast focusing, and sample screening.

Note: Pulse models include a CS-Mount to C-Mount adapter ring. All models include a USB3 cable, Basler Microscopy software, and Quick Install Guide.