

Schneider 100mm F-Mount Lens, Short WD



Stock #85-189 [CONTACT US](#)

⊖ 1 ⊕ €2.786⁰⁰

[ADD TO CART](#)

Volume Pricing

Qty 1+	€2.786,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Product Family:
Schneider Large Format F-Mount VIS-NIR Lenses

Note:
Optimized Working Distance: 644 - 2046mm

Type:
Fixed Focal Length Lens

Physical & Mechanical Properties

Iris Option:
Variable

93.70	Length (mm):
60.0	Maximum Diameter (mm):
60	Outer Diameter (mm):
463.00	Weight (g):
0.0	Maximum Rear Protrusion (mm):

Optical Properties

216.00	Field of View @ Min Working Distance (mm):
20.4°	Horizontal Field of View, 35mm Sensor:
43.30	Maximum Image Circle (mm):
100.00	Focal Length FL (mm):
421 - ∞	Working Distance (mm):
f/2.8 - f/22	Aperture (f/#):
<0.5	Distortion (%):
400 - 1000 BBAR	Coating:
VIS-NIR Color Corrected	Lens Wavelength Range:

Sensor

35mm (43.3mm Image Circle)	Maximum Sensor Format:
6.20	Pixel Size (µm):

Threading & Mounting

M43.0 x 0.75	Filter Thread:
F-Mount	Mount:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

Product Details

- Full Frame, 35mm (Covers 46mm Image Circle), F-Mount Lens
- Color Corrected for Spectral Range of 400 – 1000nm
- 28mm to 100mm Focal Length

Ideal for surface inspection and line scan applications, Schneider Large Format F-Mount MS-NIR Lenses offer low distortion and uniform performance across the entire focal plane. Featuring a lockable focus and iris, these lenses have been optically corrected for the 400 – 1000nm wavelength range. They can cover up to 35mm format sensors (43.3mm sensor diagonal). Schneider Large Format F-Mount MS-NIR Lenses has been highly toleranced to eliminate tilt in the image plane, providing repeatable and accurate results.