


[See all 31 Products in Family](#)

SCHOTT EasyLED Ring Light

See More by [SCHOTT Optical Components](#)



Stock #15-905 **3 In Stock**

− 1 + €690⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€690,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

Operating Lifetime (hours):
>50,000

Model Number:
600.200

Intensity Control Option:

Yes

Number of LEDs:

45

Type of Illumination:

LED Illuminator

Manufacturer:

SCHOTT

Geometry:

Ring Light

Illumination Mode:

Constant

Physical & Mechanical Properties

Inner Diameter (mm):

66

Outer Diameter (mm):

114

Optical Properties

Color:

White

Working Distance (mm):

55 - 135

Hardware & Interface Connectivity

Input Voltage (V):

12 DC

Power Supply:

Power supply included. If additional power supplies are required, see [#15-907](#)

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Ringlight, Backlight, and Spotlight Illuminators
- Integrated Controllers for Intensity Adjustment
- Designed for Easy Integration into Microscopy Systems

SCHOTT EasyLED Series Illuminators are compact illuminators with integrated controllers that provide continuous intensity adjustment. These illuminators are available as ringlights, backlights, or spotlights, and accessories are available to integrate each type of illuminator into microscopy systems. EasyLED Ringlights offer homogenous, shadow-free illumination, while the Ringlights Plus also features controllable LED segments for enhanced contrast adjustment. EasyLED Backlights are designed to fit common microscope stand sizes from 84 to 180mm in diameter and provide uniform illumination over their large 50mm diameter active area. EasyLED Spotlights can be mounted to any microscope stand to facilitate integration into existing microscopy systems and are available with one or two adjustable spotlights. SCHOTT EasyLED Series Illuminators are an ideal replacement for conventional cold light sources using fiber optics in machine vision or microscopy applications.

Technical Information

System Diagram for EasyLED Series

