

[See all 4 Products in Family](#)

## Silicon Based Touchscreen Portable Laser Power Meter



Silicon Based Touchscreen Portable Laser Power Meter, #34-514

Stock **#34-514** **2 In Stock**

⊖ 1 ⊕ €2.060<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	€2.060,00 each
Qty 5+	€1.855,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Operating Lifetime (hours):  
17

Response Time (s):  
0.2

Type of Display:  
Touch screen color LCD

Note:  
USB Port Available for Data Transfer

## Physical & Mechanical Properties

212.00	<b>Length (mm):</b>
150.00	<b>Weight (g):</b>
41.00	<b>Width (mm):</b>
15.0	<b>Depth (mm):</b>
7.00	<b>Accuracy (%):</b>

## Optical Properties

320 - 1100	<b>Wavelength Range (nm):</b>
320 - 1100nm (attenuator Off) 400 - 1100nm (attenuator On)	<b>Spectral Range:</b>

## Sensor

10 x 10	<b>Maximum Sensor Size (mm):</b>
---------	----------------------------------

## Electrical

36 (attenuator Off) 300 (attenuator On)	<b>Incident Power (mW):</b>
100.00	<b>Maximum Incident Power Density (W/cm<sup>2</sup>):</b>
0.3 nW - 36 mW @ 980nm (attenuator Off) 3 nW - 300 mW @ 980nm (attenuator On)	<b>Power Range:</b>
10 @ 980nm	<b>Noise Equivalent Power (pW):</b>

## Hardware & Interface Connectivity

USB Rechargeable Battery	<b>Power Supply:</b>
--------------------------	----------------------

## Threading & Mounting

8-32 threaded (x1)	<b>Mounting Hole for Screw:</b>
--------------------	---------------------------------

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 242:</b>

## Product Details

- Small Portable Design with Touchscreen Display
- Computer and Software Not Required
- High Damage Threshold
- USB Rechargeable Battery

Touchscreen Portable Laser Power Meters feature LCD displays with touchscreen controls, the ability to adjust wavelength, brightness and screen orientation, and min/max display. Available in two designs, one as a silicon based sensor and the other an absorber, these portable power meters can transfer data to a computer for data logging via a mini USB port. The silicon sensor model (#34-514) features a folding body design with a click stop at 90 degrees, providing the unique ability of being placed on an optical table unmounted when oriented at 90 degrees. If the beam height is 78mm off the optical table, you can simply set the folded power meter directly onto the table. Both Touchscreen Portable Laser Power Meter models feature 8-32 mounting holes for table top mounting and rechargeable battery.

**Note:** Mini-USB cable not included.