

TECHSPEC® Sliding 2" x 3" Base Plate



Stock #03-655 **20+ In Stock**

- 1 + €25²⁵

ADD TO CART

Volume Pricing	
Qty 1-9	€25,25 each
Qty 10+	€22,50 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

English Type:

Physical & Mechanical Properties

76.20 Length (mm):

50.80 Width (mm):

9.50 **Thickness (mm):**

Black Anodized Aluminum **Construction:**

2 **Number of Slots:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 250:**

Product Details

- Increase the Versatility of Existing Mounting Equipment
- Ideal for Direct Mounting to Standard Breadboards
- Counterbored 1/4-20 or M6 x 1.0 Holes/Slots

TECHSPEC® Slotted 2" x 3" Base Plates are versatile mounting surfaces for breadboard and optical rail applications. Three 6.4mm diameter counterbored holes, ideal for 1/4"-20 hardware, allow posts or post holders to be mounted directly and can also accommodate a variety of other optomechanical components. The plates are ideal for adding extra versatility and adjustment capability to a benchtop optical system. TECHSPEC® Slotted 2" x 3" Base Plates are available in standard sliding or side to side sliding configurations, allowing for adjustment along or perpendicular to the optical axis of the system.

Technical Information

