

[See all 2 Products in Family](#)

Solid State UV Flood Light Systems (Recertified 05-P)



Solid State UV Flood Light Systems

Stock #16-762-RCD-05P RECERTIFIED **1 In Stock**

⊖ 1 ⊕ €2.250⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€2.250,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Operating Lifetime (hours):
>20,000

Physical & Mechanical Properties

Dimensions (mm):
UV Curing Head: 55 x 52 x 148
Control Box: 160 x 150 x 80

Optical Properties

Wavelength (nm):

380.00 ±5

Beam Size (mm):

50 x 50mm (30mm WD)
100 x 100mm (100mm WD)

Working Distance (mm):

30 - 100

Irradiance (W/cm²):

0.8

Hardware & Interface Connectivity

Power Requirement:

AC 100 - 240V

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Large, Uniform UV Light Output
- 380nm Center Wavelength
- Up to 0.8W/cm² UV Irradiance

Solid State UV Flood Light Systems produce a large, uniform output beam of UV light centered at 380nm. These systems consist of a controller box with a built-in timer for automated curing and a handheld UV flood light with an on-off switch. The controller box features integrated heat sinks and a cooling fan, allowing for continuous operation without a change in UV intensity. Solid State UV Flood Light Systems are ideal for UV curing applications, especially those with either large components or multiple small components to cure.