

## SWIR 1200nm Adjustable Ring Light



EffluxSMR LED Ring Lights

Stock #28-623 [CONTACT US](#)

- 1 + €3.996<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€3.996,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

EFFI-RING-1200-KIT-CW **Model Number:**

- **Number of LEDs:**

LED Illuminator **Type of Illumination:**

>90% **Uniformity (%):**

**Manufacturer:**

Effilux

Ring Light

Geometry:

Strobed or Constant

Illumination Mode:

## Physical & Mechanical Properties

58.0

Inner Diameter (mm):

151.0 W x 117.0 L x 40.0 H

Dimensions (mm):

400

Weight (g):

100 x 100

Active Area (mm):

## Optical Properties

SMIR

Color:

1,200

Wavelength (nm):

## Hardware & Interface Connectivity

M12, 5 pins

Connector:

24VDC

Input Voltage (V):

Power Supply:

Power Supply Required and Sold Separately.

USA: [#15-874](#)

Europe: [#15-875](#)

Japan: [#73-409](#)

Korea: [#73-409](#)

China: [#15-874](#)

## Threading & Mounting

M4 (x4) and 3.5mm Thru (x4)

Mount:

## Environmental & Durability Factors

-10 to 50

Operating Temperature (°C):

IP65

Environmental Rating:

## Regulatory Compliance

[View](#)

Certificate of Conformance:

## Product Details

- Full Range of SMIR Wavelengths Available
- High Intensity and Uniform Lighting
- Adjustable Illumination Angles

Effilux SMIR LED Ring Lights provide intense and uniform lighting for machine vision, sorting and silicon inspection applications. Available in wavelengths of 1050, 1200, 1300, 1450, 1550, and 1650nm. These ring lights feature adjustable lens positions and illumination angles for added flexibility. Effilux SMIR LED Ring Lights are ideal complements for applications utilizing TECHSPEC® C Series Fixed Focal Length SMIR Lenses, TECHSPEC® SilverTL™ SMIR Telecentric Lenses and LUCID Vision Labs Triton™ GigE Power over Ethernet (PoE) SMIR Cameras or Teledyne FLIR IIS Forge 1GigE SMIR Cameras.

**Note:** Included with the ring lights are one semi diffuse window and one 25° lens position kit.

[3D-Printable Mount Files](#)



Ring Light Configuration

[Download Now](#)

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to ¼-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



**Application Note**

Illumination Mounts for Machine Vision Applications

[Read](#) 



**Video**

Assembly of 3D Printed Mounts for Common Illumination Geometries

[Watch](#) 