

[See all 15 Products in Family](#)

WinCamD-LCM TEL Beam Profiler



Stock #91-096 **NEW** 1 In Stock

- 1 + €8.380⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€8.380,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Model Number:
S-WCD-LCM-TEL

Contents of Kit:
Includes magnetic 1" ND filters (MagND-1, MagND-2, MagND-4, 1290nm Longpass Filter).

Physical & Mechanical Properties

Dimensions (mm):
46 x 46 x 20

Dimensional Accuracy:

±2µm

Optical Properties

1480 - 1610 **Spectral Range:**

USB 2.0: 6.3 kHz
USB 3.0: 12.6 kHz **Minimum Stimulation, Pulsed:**

55 (10 Pixels) **Beam Diameter (µm):**

Sensor

5.5 x 5.5 **Pixel Size, H x V (µm):**

2,048 x 2,048 **Pixels (H x V):**

11.3 x 11.3 **Sensing Area, H x V (mm):**

1" **Sensor Format:**

≥12 **Frame Rate:**

Electrical

2,500:1 **Signal to Noise S/N Ratio (dB):**

34 dB optical / 68 dB electrical **Peak Noise (nW/cm²):**

Threading & Mounting

8-32 thread, 8 mm deep **Mount:**

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

Product Details

- Designed for Use from 355 to 16000nm
- Compatible with Beam Diameters Down to 52µm
- Robust and Easy to Use Free Software [Provided](#)
- Measure Beam Wander, M_r, Divergence, and More

DataRay Camera Beam Profilers provide excellent solutions for beam analysis of both continuous wave and pulsed laser sources. Each beam profiler features an integrated CMOS sensor (IR profilers feature Microbolometer sensors) that eliminates comet trailing for higher resolution output and allows for update rates of 60+ Hz. Sensors are available with active sizes of 6.6, 11.3, and 25mm horizontals, enabling measurement of large beam diameters. DataRay Camera Beam Profilers have the added advantage of a free, robust software with analysis features such as M_r measurement, beam wander and logging, and instrument alignment. These profilers are USB3.0/2.0 powered and include a 3m flexible screw locking cable. Neutral density filters with optical densities of 1.0, 2.0, and 4.0 are included.